



SPECIFICATIONS				
OPERATING VOLTAGE	10-30 VDC			
RIPPLE	≤ 10%			
DIFFERENTIAL TRAVEL (HYSTERESIS)	3-15% (5% TYPICAL)			
VOLTAGE DROP ACROSS CONDUCTING SENSOR	≤ 1.8 V at 200 mA			
OUTPUT FUNCTION	NORMALLY OPEN 3-WIRE DC SELF-CONTAINED			
SHORT-CIRCUIT PROTECTED	YES ≥ 220 mA			
TRIGGER CURRENT FOR OVERLOAD PROTECTION				
CONTINUOUS LOAD CURRENT	≤ 200 mA			
OFF-STATE (LEAKAGE) CURRENT	≤ 0.1 mA			
NO-LOAD CURRENT	≤ 15 mA			
TIME DELAY BEFORE AVAILABILITY	≤ 8 ms			
POWER-ON EFFECT	PER IEC 947-5-2			
REVERSE POLARITY PROTECTION	INCORPORATED			
WIRE-BREAK PROTECTION	INCORPORATED			
PROTECTION AGAINST TRANSIENTS	Per EN 60947-5-2			
OPERATING TEMPERATURE (10% DRIFT)	-25°C to +70°C (-13°F to +158°F)			
OPERATING TEMPERATURE (15% DRIFT)	-30°C to +85°C (-22°F to +185°F)			
ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP68			
SHOCK	30 g, 11 ms			
VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)			
LED FUNCTION	LED ON: OUTPUT ENERGIZED			
	LED FLASHING: SHORT-CIRCUIT WARNING			
RATED OPERATING DISTANCE(Sn)	12 mm = .472" (NOMINAL)			
SWITCHING FREQUENCY	2000 Hz			
REPEATABILITY	≤ 2% of RATED OPERATING DISTANCE			
EMBEDDABLE (SHIELDED)	NO			
MATING PLUGS/CABLES	4-PIN "EUROFAST" CONSTRUCTION			

NOTES:

1. UPROX HAS WELD FIELD IMMUNITY, SENSOR IS SUITABLE FOR USE ON RESISTANCE MACHINES.

А	UPDATE SENSOR GEOMETRY	СВМ	09/27/99	T3089
REV	DESCRIPTION	BY	DATE	ECO NO.

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	Sensors and Automation Controls	3000 CAMPUS DRIVE MINNEAPOLIS, MN 5544 1 -800-544-7769 (763) 553-7300 (763) 553-0708 fa turck.com	
	MATERIAL BRASS BARREL		DRFT IK	DATE 07/28/99	DESCRIPTION Ni12U-M18-AP	EV 111141	
	DIASS DANNEL	ALL DIMENSIONS DISPLAYED ON THIS	DSGN	SCALE NONE	NIIZU-MIO-AP	0X-H1141	
E		DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT		I I I I I I I I I I I I I I I I I I I		55.4
	FINISH			IDENTIFICATION NO.			REV
	COPPER/NICKEL	CONTACT TURCK FOR MORE		LIMETER]	M16451	40	ΙΑ
89	CHROME PLATING	INFORMATION					, ,
NO.			DO NOT SCALE	THIS DRAWING	FILE: M1645140	SHEET	1 OF 1