



M12 Rail PG Clamp

TE Internal #: 1-2312527-2

5 Position Circular Connector, Cable-to-Cable, Sealable, Wire & Cable, Signal, Reverse Gender, Plastic, A Code, M12 Rail PG Clamp

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Straight D4 PG Clamp



Number of Positions: 5

Connector System: **Cable-to-Cable**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **4 A**

[All M12 Straight D4 PG Clamp \(12\)](#)

Features

Product Type Features

Assembly Requirement	Factory Assembled
Circular Connector Shell Type	All Plastic
Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Prewired	No
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Plastic

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	With



Number of Positions	5
Number of Power Positions	0
Number of Signal Positions	5
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	50 VDC
EMI & RFI Protection & Suppression Type	Shielding

Body Features

Product Weight	25 g[.8832 oz]
Environmental Protection	IP67
Environmental Protection Type	Sealed
Primary Product Color	Black
Shell Base Material	Plastic
Circular Connector Insulation Material Type	Low Fire Hazard Thermoplastic
Hermetically Sealed	Yes

Contact Features

Contact Current Rating (Max)	4 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention Type	Threaded
Mating Alignment	With
Polarization Code	A
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	19
-------------------------------	----

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	IP67



Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	250 Cycles
Circuit Application	Signal
Shielded	Yes

Industry Standards

Compatible With Approved Standards Products	IEC
---	-----

Packaging Features

Packaging Quantity	1
--------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3.5% in Component Part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts




TE Part # 1-2823557-1  
CRIMP TOOL FOR CRIMP FLANGE /SLEEVE




TE Part # 1-2823560-1  
ASSEMBLY TOOL HANDLE FOR CRIMP FLANGE




TE Part # 1-2314102-1  
M12 CRIMP CONTACT PIN 1 MM AU 0.8 AWG20




TE Part # CAT-R131-IN722  
Crimp Insert for Use with 1-2823557-1




TE Part # 601967-1  
CRIMPING TOOL M22520/1-01



TE Part # 1-2823561-1  
UNIVERSAL INSERT (ALL M12 CODES)




TE Part # CAT-M1-M1  
M12 Assembly Tooling



TE Part # 601966-1  
CRIMPING TOOL M22520/2-01

Also in the Series | M12 Rail PG Clamp



Standard Circular Connectors(22)

Customers Also Bought



TE Part #1703013-1  
DIA 1.5MM CONTACT PIN,ASSY



TE Part #1622447-1  
LR1 1% 360R




TE Part #1718230-1  
1,5MM PIN HSG 5-7 POS ASSY



TE Part #5787170-7  
68 50SR R/A RCPT ASSY,RDSN L/F





TE Part #5227699-1  
BNC PCB VERTICAL

TE Part #1SNS420967Z0000  
C.M7.77.030.24-- (XT19.521)

TE Part #6-1768383-4  
LBF-2000P-RIBBON-1966-MED

TE Part #1SNS421074Z0000  
BN11.BT.V14A- (ENT14886 A)

TE Part #1SNS420966Z0000  
C.M7.77.030.23-- (XT19.511)

TE Part #1SNS420608Z0000  
C.M7.77.030.22-A (XT70.103)

Documents

Product Drawings  
M12 A-CODED M-5 CABLE GLAND CONECTR MALE  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_1-2312527-2\_B.3d\_stp.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1-2312527-2\_B.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1-2312527-2\_B.3d\_igs.zip  
English

3D PDF  
3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages  
M12 Rail Straight Connector  
English