


## Technical data

### NA69/22R

Needle roller bearing, machined-ring, with inner ring

Needle roller bearing, machined-rings, with inner ring, double-side ribs, lubrication hole

#### VISUAL (S)



#### PRODUCT DEFINITION

|                                               |         |
|-----------------------------------------------|---------|
| Brand                                         | NTN     |
| d - Internal diameter                         | 22 mm   |
| D - External diameter                         | 39 mm   |
| C - Width of bearing, drawn cup or outer ring | 30 mm   |
| F - Under roller diameter                     | 28 mm   |
| rs - Min fillet radius                        | 0,3 mm  |
| s - Max axial offset                          | 0,5 mm  |
| Lubrication hole on outer ring                | Oui/Yes |



#### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

# NA69/22R

Needle roller bearing, machined-ring, with inner ring

## PRODUCT DEFINITION

|                                       |          |
|---------------------------------------|----------|
| <b>k - Hole diameter</b>              | 2,5 mm   |
| <b>Lubrication hole on inner ring</b> | Non/No   |
| <b>Radial clearance class</b>         | CN       |
| <b>Precision class</b>                | P0       |
| <b>Mass</b>                           | 0,154 kg |

## PRODUCT PERFORMANCE

|                                               |              |
|-----------------------------------------------|--------------|
| <b>Cr - Dynamic load rating</b>               | 40 kN        |
| <b>C0r - Static load rating</b>               | 58,5 kN      |
| <b>N lim - Grease lubrication limit speed</b> | 9500 tr/min  |
| <b>N lim - Oil lubrication limit speed</b>    | 14000 tr/min |
| <b>Tmin - Min operating temperature</b>       | -20 °C       |
| <b>Tmax - Max operating temperature</b>       | 120 °C       |

## ABUTMENT

|                                                        |        |
|--------------------------------------------------------|--------|
| <b>da min - Min shoulder diameter IR</b>               | 24 mm  |
| <b>Da max - Max shoulder diameter OR</b>               | 37 mm  |
| <b>ras max - Max shaft &amp; housing fillet radius</b> | 0,3 mm |

## ESHOPDONOTDISPLAY

|                                 |                              |
|---------------------------------|------------------------------|
| <b>Tracepart</b>                | Oui/Yes                      |
| <b>Reference</b>                | NA69/22R                     |
| <b>Image</b>                    | NRBNA59_1.jpg, NRBNA59_3.jpg |
| <b>Rolling element material</b> | Acier 100Cr6                 |



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15