

704777

# High-Low Brush, 265 mm, Medium, Lime



Effectively clean and scrub floor-wall junctions and under machines and equipment with this High-Low Brush, featuring an angled thread that lets you use the brush with the handle positioned parallel to the floor. Also ideal for cleaning drains and gulleys.

# Technical Data

<b>Item Number</b>	704777
<b>Visible bristle length</b>	41 mm
<b>Material</b>	Polypropylene Polyester Stainless Steel (AISI 304)
<b>Complies with (EC) 1935/2004 on food contact materials<sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	320 Pcs.
<b>Quantity Per Layer (Pallet)</b>	40 Pcs.
<b>Box Length</b>	610 mm
<b>Box Width</b>	300 mm
<b>Box Height</b>	210 mm
<b>Length/Depth</b>	265 mm
<b>Width</b>	150 mm
<b>Height</b>	100 mm
<b>Gross Weight</b>	0,56 kg
<b>Net Weight</b>	0,5 kg
<b>Cubik metre</b>	0,004 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. cleaning temperature (Dishwasher)</b>	93 °C
<b>Max. usage temperature (for food contact)</b>	80 °C
<b>Max usage temperature (non food contact)</b>	100 °C
<b>Min. usage temperature<sup>3</sup></b>	-20 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705022014640
<b>GTIN-14 Number (Box quantity)</b>	15705028014672
<b>Commodity Code</b>	96039099
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.