## XCPR2110P20

limit switch XCPR - metal end plunger - 1NO +1NC - snap - M20



## Main

|                               | 0 :0  |
|-------------------------------|---|
| Range of product              | OsiSense XC   |
| Series name                   | Standard format   |
| Product or component          | Limit switch  |
| type                          |   |
| Device short name             | XCPR  |
| Sensor design                 | Compact   |
| Body type                     | Fixed   |
| Head type                     | Plunger head  |
| Material                      | Plastic   |
| Body material                 | Plastic   |
| Movement of operating head    | Linear  |
| Type of operator              | Metal spring return plunger   |
| Switch actuation              | On end  |
| Type of approach              | 1 direction vertical approach   |
| Electrical connection         | Screw-clamp terminals , clamping capacity: 1 x 0.342 x 1.5 mm²          |
| Cable entry                   | 1 entry tapped for M20 x 1.5 cable gland , cable outer diameter: 713 mm |
| Number of poles               | 2   |
| Contacts type and composition | 1 NC + 1 NO   |
| Contacts operation            | Snap action   |
| Maximum actuation speed       | 0.5 m/s   |

## Complementary

| Complementary                          |  |
|--|--|
| Reset                                  | With   |
| Head material                          | Zamak  |
| Fixing mode                            | By the body  |
| Contacts insulation form               | Zb   |
| Positive opening                       | With   |
| Positive opening minimum force         | 45 N   |
| Minimum force for tripping             | 15 N   |
| Contact code designation               | A300 , AC-15 (Ue = 240 V , Ie = 3 A), Ithe = 10 A conforming to EN/IEC 60947-5-1 appendix A Q300 , DC-13 (Ue = 250 V , Ie = 0.27 A) conforming to EN/IEC 60947-5-1 appendix A  |
| [Ui] rated insulation voltage          | 300 V conforming to UL 508 300 V conforming to CSA C22-2 No 14 500 V degree of pollution 3 conforming to IEC 60947-1 500 V degree of pollution 3 conforming to EN 60947-1  |
| Resistance across terminals            | ≤ 25 mOhm conforming to IEC 60255-7 category 3   |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947-1<br>6 kV conforming to IEC 60664   |
| Short circuit protection               | 10 A by gG cartridge fuse  |
| Electrical durability                  | 5000000 cycles , DC-13 , 24 V , 10 W , load factor: 0.5 , operating rate: ≤ 60 cyc/mn 5000000 cycles , DC-13 , 48 V , 7 W , load factor: 0.5 , operating rate: ≤ 60 cyc/mn 5000000 cycles , DC-13 , 120 V , 4 W , load factor: 0.5 , operating rate: ≤ 60 cyc/mn |
| Width                                  | 31 mm  |

| Height         | 65 mm    |
|----------------|----------|
| Depth          | 30 mm    |
| Product weight | 0.115 kg |

## **Environment**

| Shock resistance                           | 50 gn (duration = 11 ms) conforming to IEC 60068-2-27                                   |
|--|---|
| Vibration resistance                       | 25 gn (f = 10500 Hz) conforming to IEC 60068-2-6  |
| IP degree of protection                    | IP66 conforming to IEC 60529<br>IP67 conforming to IEC 60529                            |
| IK degree of protection                    | IK04 conforming to EN 50102   |
| Class of protection against electric shock | Class II conforming to IEC 61140<br>Class II conforming to NF C 20-030                  |
| Ambient air temperature for operation      | -2570 °C  |
| Ambient air temperature for storage        | -4070 °C  |
| Protective treatment                       | TC  |
| Product certifications                     | CSA<br>UL   |
| Standards                                  | CSA C22-2 No 14<br>EN 60204-1<br>EN 60947-5-1<br>IEC 60204-1<br>IEC 60947-5-1<br>UL 508 |
| RoHS EUR conformity date                   | 4Q2009  |
| RoHS EUR status                            | Will be compliant   |

