

# SSMK 96X30 - Control cabinet marker



5032442

<https://www.phoenixcontact.com/in/products/5032442>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Control cabinet marker, size: 96 x 30 mm, lettering field: 92 x 26 mm, 2 mounting holes M3, including 1 x ES-SSMK-GB 96 x 30

## Your advantages

- The ES-SSMK ... insert strips can be labeled using the CMS-P1-PLOTTER and the CMS-P1-PAD magazine
- The labeling is resistant to external influences
- The base carrier has two fixing holes so that it can be screwed on
- Control cabinet markers consisting of a transparent cap and base carrier
- Once labeled, the insert label is inserted in the cap and this is then snapped onto the base carrier

## Commercial data

Item number	5032442
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	BG2
Product key	BG241B
Catalog page	Page 352 (C-3-2019)
GTIN	4017918095819
Weight per piece (including packing)	10.444 g
Weight per piece (excluding packing)	10.444 g
Customs tariff number	39269097
Country of origin	PL

# SSMK 96X30 - Control cabinet marker



5032442

<https://www.phoenixcontact.com/in/products/5032442>

## Technical data

### Notes

General	Can be labeled with CMS
---------	-------------------------

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	96 mm
Text field width	92.00 mm
Text field height	26.00 mm
Length	30 mm
Drill hole spacing	75.00 mm
Hole diameter	3.50 mm

### Material specifications

Color	multicolored
	white (RAL 9010)
	transparent
Material	PC
Flammability rating according to UL 94	V2
Base element material	PC
Components	free from silicone and halogen

### Mechanical properties

#### Technical data

Drill hole spacing	75.00 mm
--------------------	----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

### Mounting

Mounting type	screw, rivet
---------------	--------------

# SSMK 96X30 - Control cabinet marker



5032442

<https://www.phoenixcontact.com/in/products/5032442>

## Classifications

### ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SSMK 96X30 - Control cabinet marker



5032442

<https://www.phoenixcontact.com/in/products/5032442>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# SSMK 96X30 - Control cabinet marker



5032442

<https://www.phoenixcontact.com/in/products/5032442>

## Accessories

### ES-SSMK-GB 96X30 - Insert strip

5032455

<https://www.phoenixcontact.com/in/products/5032455>

Insert strip, Sheet, transparent/white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, mounting type: insert, Number of individual labels: 22, text field height: 26 mm, text field width: 92 mm



---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)