

PML-C101 (D39)R - Label



1032780

<https://www.phoenixcontact.com/gb/products/1032780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2: pre-printed, mounting type: adhesive, Number of individual labels: 500, text field height: 39 mm, text field width: 39 mm

Your advantages

- Adhesive circuit identification label, color preprinted
- Highly flexible, soft PVC label that adapts well to uneven surfaces
- When high-quality ink ribbons are used, the marking is resistant to solvents and suitable for use even under harsh industrial conditions.
- PVC label is outdoor-durable for up to eight years when used within a temperature range of -50°C ... 90°C

Commercial data

Item number	1032780
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG2611
Product key	BG2611
Catalog page	Page 384 (C-3-2019)
GTIN	4055626537184
Weight per piece (including packing)	278.5 g
Weight per piece (excluding packing)	278.5 g
Customs tariff number	39199080
Country of origin	DE

PML-C101 (D39)R - Label

1032780

<https://www.phoenixcontact.com/gb/products/1032780>



Technical data

Product properties

Product type	Warning label printed
Area of application	Circuit marking on emergency lighting in accordance with DIN VDE 0108-100
Type	circular

Marking

Number of individual labels	500
Number of individual labels per row	1
Printing	pre-printed

Dimensions

Width	39 mm
Height	39 mm

Text field

Text field width	39 mm
Text field height	39 mm

Material specifications

Color	white/red
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

TesaFilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Duration	96 h

PML-C101 (D39)R - Label

1032780

<https://www.phoenixcontact.com/gb/products/1032780>



Temperature for testing	120 °C
-------------------------	--------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

PML-C101 (D39)R - Label

1032780

<https://www.phoenixcontact.com/gb/products/1032780>



Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PML-C101 (D39)R - Label

1032780
<https://www.phoenixcontact.com/gb/products/1032780>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk