



## Main

|                           |  |
|---------------------------|--|
| Range of product          | Harmony XVM  |
| Product or component type | Base unit kit  |
| Kit composition           | Bracket<br>250 mm support tube<br>Base unit<br>Cover |
| Component name            | XVM  |
| Indicator bank base type  | Base without buzzer                                  |

## Complementary

|                         |  |
|-------------------------|--|
| Mounting diameter       | 45 mm  |
| Housing colour          | White  |
| Connections - terminals | Screw terminals, 1 x 0.325...1 x 1.5 mm <sup>2</sup> |
| Marking                 | CE   |
| Net weight              | 0.298 kg   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | EN/IEC 60947-1<br>EN/IEC 60947-5-1  |
| Product certifications                | CCC   |
| Ambient air temperature for storage   | -25...70 °C   |
| Ambient air temperature for operation | -10...50 °C   |
| Electrical shock protection class     | Class I aluminium tube mounting conforming to IEC 60947-1<br>Class I aluminium tube mounting conforming to IEC 60947-5-1<br>Class I aluminium tube mounting conforming to IEC 61140 |
| IP degree of protection               | IP40 any position except vertical position conforming to IEC 60529<br>IP42 vertical position conforming to IEC 60529  |
| Protective treatment                  | TC  |

## Offer Sustainability


|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           |  <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes  |
| RoHS exemption information |  <a href="#">Yes</a>  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Customer Assembled Tower Light

### Wiring Diagram



Indicator bank with buzzer (4 illuminated units max.):

- 4: 4th illuminated unit
- 3: 3rd illuminated unit
- 2: 2nd illuminated unit
- 1: 1st illuminated unit
- N: Common
- B: Buzzer

Indicator bank without buzzer:

- 5: 5th illuminated unit
- 4: 4th illuminated unit
- 3: 3rd illuminated unit
- 2: 2nd illuminated unit
- 1: 1st illuminated unit
- N: Common

Maximum capacity for wiring through support tube:

- 6 wires x 1 mm<sup>2</sup>/16 AWG,
- 5 wires x 1.5 mm<sup>2</sup>/14 AWG