

# Product data sheet

Specifications



Repacked Monolithic pilot light,  
Harmony XB5, 3 phases Voltage,  
indicator with 3 LED, white, 400V  
AC

XB5EV57L4W

 **This repacked option saves 0.575 over the standard condition**

## Main

|                               |                        |
|-------------------------------|------------------------|
| Range of product              | Harmony XB5            |
| Product or component type     | Monolithic pilot light |
| Device short name             | XB5                    |
| Bezel material                | Plastic                |
| Fixing collar material        | Plastic                |
| Mounting diameter             | 30 mm                  |
| Sale per indivisible quantity | 1                      |
| Shape of signaling unit head  | Round                  |
| Cap/operator or lens colour   | Clear                  |
| Light source                  | Protected LED          |
| Bulb base                     | Integral LED           |
| Light source colour           | White                  |
| Network number of phases      | 3 phases               |
| Device presentation           | Monolithic product     |

## Complementary

|                                        |                                                                     |
|----------------------------------------|---------------------------------------------------------------------|
| Height                                 | 65.5 mm                                                             |
| Width                                  | 36 mm                                                               |
| Depth                                  | 77 mm                                                               |
| Product weight                         | 0.065 kg                                                            |
| Connections - terminals                | Faston terminals, connection size: 6.3 mm conforming to IEC 60947-1 |
| [Uimp] rated impulse withstand voltage | 1 kV conforming to IEC 61000-4-5                                    |
| Compatibility code                     | XB5                                                                 |
| Supply voltage limits                  | 450 V AC                                                            |
| Current consumption                    | 5...8 mA                                                            |
| Service life                           | 100000 h at rated voltage and 25 °C                                 |
| Surge withstand                        | 1 kV conforming to IEC 61000-4-5                                    |

## Environment

|                                     |             |
|-------------------------------------|-------------|
| Ambient air temperature for storage | -40...70 °C |
|-------------------------------------|-------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                                                                                                                                                                                                                    |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient air temperature for operation | -30...70 °C                                                                                                                                                                                                        |
| IP degree of protection               | IP67 (front face)<br>IP20 (back face)                                                                                                                                                                              |
| IK degree of protection               | IK10 conforming to IEC 50102                                                                                                                                                                                       |
| Standards                             | IEC 60947-5-1<br>IEC 60947-5-4<br>IEC 60947-1                                                                                                                                                                      |
| Resistance to fast transients         | 2 kV conforming to IEC 61000-4-4                                                                                                                                                                                   |
| Resistance to electromagnetic fields  | 10 V/m conforming to IEC 61000-4-3                                                                                                                                                                                 |
| Electromagnetic compatibility         | Electrostatic discharge - test level: 8 kV (in free air (in insulating parts)) conforming to IEC 61000-4-2<br>Electrostatic discharge - test level: 4 kV (on contact (on metal parts)) conforming to IEC 61000-4-2 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 4.000 cm |
| Package 1 Width              | 4.500 cm |
| Package 1 Length             | 9.000 cm |
| Package 1 Weight             | 64.000 g |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

0.6 kg CO2 eq.

## Use Better



### Materials and Substances

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---





