

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 125MM

Fixed

KF41BA125-325RX



Part Number

Swivel

KP41BA125-325RX




Swivel and brake

KP41BD125-325RX



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	125 mm		
Overall Height H	155 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	38 mm	38 mm
Width of Tread	32 mm±0,5		
Hardness of tread	shore A ± 88		
Load capacity	100 Kg		
Weight	0,65 kg	0,78 kg	0,93 kg
Temperature	- 10 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
Tread : Thermoplastic rubber, grey non marking.
Hub : Stainless steel Roller bearing.

Features :

Low starting effort,
Bonded Rubber,
Corrosion resistant, easy to clean
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Medium duty.