



SCALANCE MUB852-1 (A1) 5G router, IP20, for wireless IP communication from Ethernet-based applications via public 3G/4G/5G mobile radio networks and private 5G networks, VPN (in combination with SINEMA RC device license) firewall, NAT, IPv6, connection to SINEMA RC, 4 SMA connections, 1x nano SIM slot, 1x10/100/1000 Mbps RJ45 port, 24 V DC 0 to +55 °C, region version A1 observe national approvals! siemens.com/mobile-approvals CERT ID: EL5G16R-20-M1-RJ-E4-1

product brand name	SCALANCE
Technical Product Detail Page	https://i.siemens.com/1P6GK5852-1EA10-1AA1
transfer rate	
transfer rate / for Industrial Ethernet	10, 100, 1000 Mbit/s
transfer rate	
• with UMTS transmission / with downlink / maximum	42 Mbit/s
• with UMTS transmission / with uplink / maximum	5.76 Mbit/s
• for LTE transmission / with downlink / maximum	1000 Mbit/s
• for LTE transmission / with uplink / maximum	200 Mbit/s
• for 5G transmission / with downlink / maximum	1000 Mbit/s
• for 5G transmission / with uplink / maximum	500 Mbit/s
interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of electrical/optical connections / for gigabit Ethernet / maximum	1
number of electrical connections	
• for network components or terminal equipment	1
number of electrical connections	
• for external antenna(s)	4
• for power supply	1
type of electrical connection	
• for external antenna(s)	SMA antenna socket (50 ohms)
• for power supply	3-pin terminal strip
memory	
number of slots / for Micro-SIM card	1
product component / eSIM integrated	No
design of the removable storage / CLP	No
WAN connection	
type of wireless network / is supported	5G public networks, 5G private networks, LTE, UMTS
type of mobile wireless service / is supported	HSDPA, HSUPA, HSPA+
frequency band / is supported	
• 5G Standalone (SA)	n1, n2, n3, n5, n7, n8, n20, n25, n28, n30, n38, n40, n41, n48, n66, n71, n75(DL), n77, n78, n79
• 5G Non-Standalone (NSA)	n1, n2, n3, n5, n7, n8, n20, n25, n28, n30, n38, n40, n41, n66, n71, n77, n78, n79
• LTE	B1, B2, B3, B4, B5, B7, B8, B12, B13, B14, B17, B18, B19, B20, B25, B26, B28, B29(DL), B30, B32(DL), B34, B38, B39, B40, B41, B42, B43, B46(DL), B48, B66, B71
• UMTS	B1, B2, B4, B5, B6, B8, B19

supply voltage, current consumption, power loss	
consumed current	
• at DC / at 24 V	0.3 A
power loss [W]	
• at DC / at 24 V / typical	7.2 W
supply voltage / 1 / rated value	24 V
• type of voltage / 1 / of the supply voltage	DC
ambient conditions	
ambient temperature	
• during operation	0 ... 55 °C
• during storage	-40 ... +85 °C
relative humidity / at 25 °C / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
depth	74 mm
height	114 mm
width	50 mm
net weight	200 g
fastening method	mounting on DIN rail
• 35 mm DIN-rail mounting	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
type of configuration	Web-based management
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
product functions / diagnostics	
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v2c	Yes
• SNMP v3	Yes
product function	
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
• packet filter log	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP server - internal network	Yes
product functions / routing	
router function	
• NAT (IP masquerading)	Yes
• port forwarding	Yes
• NAT traversal	Yes
• 1:1 NAT	Yes
• DNS cache	Yes
product functions / security	
suitability for operation / Virtual Private Network	Yes
firewall version	Statefull Inspection

product function	
• password protection	Yes
• packet filter	Yes
• broadcast/multicast/unicast limiter	No
product function	
• broadcast blocking	No
type of authentication / with Virtual Private Network / PSK	No
protocol / is supported	
• IPsec tunnel and transport mode	No
type of internet key exchange / with Virtual Private Network	
• main mode	No
• quick mode	No
IETF profile / with Virtual Private Network / X.509v3 certificate	No
product functions / time	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
standards, specifications, approvals	
standard	
• for EMC	ETSI EN 301 489-1, ETSI EN 301 489-19, ETSI EN 301 489-52, EN 55011, NAMUR NE21
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Mobile radio national approval	https://www.siemens.com/mobile-approvals
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)

Approvals / Certificates

General Product Approval



[Type Examination Certificate](#)



[China RoHS](#)

Radio Equipment Type Approval Certificate

last modified:

6/24/2026 