



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold (Au)**
Wire Contact Termination Area Plating Material: **Gold**
Contact Size: **Size 20**
Wire Size: **24 – 20 AWG**

Features

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Gold
Contact Size	Size 20
Contact Current Rating (Max)	7.5 A

Dimensions

Wire Size	.25 – .5 mm²
-----------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (.7% in Contact Lead-Copper Alloy) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.




Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #521120-1
PL 250 HOUSING RECEPTACLE
NYLON 6/6




TE Part #ZPF000000000148753
DMC-M 99-04 BN (=33537-S0000)




TE Part #173631-1
MCI/O REC CONTACT REEL




TE Part #133761-000
55PC1241-20-CML4-9CS2502




TE Part #3-520124-2
187 ULTRA-FAST ASY REC 16-14 AWG
TPBR




TE Part #776428-3
AS16,CAP ASSY,ST,02P,N SEAL,CODE
C




TE Part #ZPF000000000148762
DMC-M 99-04 AN (=33537-P0000)



TE Part #323059
TERMINAL,SOLIS R HT 12-10 6



TE Part #444311-1
HSG 12 POSN, FUSE C



TE Part #776127-2
2POS .070 MULTILOCK PLUG RIGHT