



Swivel Chrome Castor, 50mm Roller, 40kg

Design Chrome Roller castor

PRODUCT

Article number	366 514	366524
		

Product Details

Castor assembly : Pressed steel, plate, bright chrome-plated protection.
 Swivel : Swivel on two rows of balls
 Rim : Transparent Polypropylene.
 Tread : Transparent Polyurethane. Non-marking.
 Hub : Plain bearing.

TECHNICAL DATA

Specifications	Plate
Wheel Diameter - ØD ± 1%	50 mm
Hub Type	Plain bore
Hub Length	21 mm ±1
Width of Tread	18mm ±1
Width of Tread-on floor	18 mm ±1
Overall Height	72 mm
Offset	23 mm
Fixing Plate Dimensions	42x42 mm
Fixing Centres	32x32 mm
Fixing Hole Size	4,5 mm
Hardness of tread A ±3	A 80° Shore
Load capacity	40 Kg
Temperature	-5 / +50 °C

Applications :

Attractive Appliances and furniture.
 Bright and roller design.
 Quiet.
 Easy to move.