



AZ 16-03ZIB1-M16

- 3 cable entries M 16 x 1.5
- Thermoplastic enclosure
- Individual coding
- Coding level "High" according to ISO 14119
- 52 mm x 90 mm x 30 mm
- Long life
- Double-insulated
- Large wiring compartment
- High level of contact reliability with low voltages and currents
- Insensitive to soiling
- Slotted holes for adjustment, circular holes for location

Data

Ordering data

Product type description	AZ 16-03ZIB1-M16
Article number (order number)	101150055
EAN (European Article Number)	4030661154497
eCl@ss number, version 12.0	27-27-26-02
eCl@ss number, version 11.0	27-27-26-02
eCl@ss number, version 9.0	27-27-26-02
ETIM number, version 7.0	EC002592
ETIM number, version 6.0	EC002592

Approvals - Standards

Certificates	cULus
--------------	-------

General data

Standards	EN ISO 13849-1 EN ISO 14119 EN IEC 60947-5-1
Coding level according to EN ISO 14119	High
Working principle	electromechanical
Housing material	Plastic, glass-fibre reinforced thermoplastic, self-extinguishing
Material of the actuator	Stainless steel
Gross weight	156 g

General data - Features

Ejection force	Yes
Number of safety contacts	3
Number of cable glands	3

Safety classification

Standards	EN IEC 60947-5-1
Performance Level, up to	c
Category	1
B _{10D} Normally-closed contact (NC)	2,000,000 Operations
Note	Electrical life on request.
Mission time	20 Year(s)

Safety classification - Fault exclusion

Please note:	Can be used when fault exclusion for dangerous damage to the 1-channel mechanism is permissible and sufficient protection against manipulation is guaranteed.
Performance Level, up to	d
Category	3
Note	for 2-channel use and with suitable logic unit.
Mission time	20 Year(s)

Mechanical data

Actuating radius, minimum	250 mm
Actuator	straight rigid
Mechanical life, minimum	1,000,000 Operations
Positive break travel	8 mm
Positive break force per NC contact, minimum	10 N
Positive break force, minimum	30 N
Actuating speed, maximum	2 m/s
Mounting	Screws
Type of the fixing screws	2x M6

Mechanical data - Connection technique

Cable entry	3 x M16 x 1,5
Termination	Screw terminals
Cable section, minimum	0.75 mm ²
Cable section, maximum	2.5 mm ²
Note	All indications including the conductor ferrules.
Allowed type of cable	solid single-wire solid multi-wire flexible

Mechanical data - Dimensions

Length of sensor	30 mm
Width of sensor	52 mm
Height of sensor	90 mm

Ambient conditions

Degree of protection	IP67
----------------------	------

Ambient temperature	-30 ... +80 °C
Storage and transport temperature	-40 ... +85 °C
Permissible installation altitude above sea level, maximum	2,000 m

Ambient conditions - Insulation values

Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	6 kV
Overvoltage category	III
Degree of pollution	3

Electrical data

Thermal test current	10 A
Required rated short-circuit current	1,000 A
Switching element	3 NC contact
Switching principle	slow action, positive break NC contact
Maximum switching frequency	4,000 /h
Material of the contacts, electrical	Silver

Electrical data - Safety contacts

Voltage, Utilisation category AC-15	230 VAC
Current, Utilisation category AC-15	4 A
Voltage, Utilisation category DC-13	24 VDC
Current, Utilisation category DC-13	4 A

Scope of delivery

Scope of delivery

Slot sealing plugs

Note

Note (General)

The axis of the hinge must be 5 mm above and in a parallel plane to the top surface of the safety switch.

Minimum actuating radius on hinged guards 250 mm

The actuator is not available separately.

Ordering code

Product type description:

AZ 16-(1)ZI-(2)-(3)

(1)

03

3 NC contact

12

1 NO contact/2 NC contacts

(2)

B1

straight design

B1-1747

straight design with magnetic latch

B1-2024

straight design with slot-lip seal

B1-2053

straight design with ball latch

B1-2177

straight design with centering guide

B6L

angled, flexible to the left

B6R

angled, flexible to the right

(3)

M16

cable entry M16

M20

Cable entry M20

Pictures

Product picture (catalogue individual photo)




ID: kaz16f11

| 674.9 kB | .jpg | 352.778 x 685.094 mm - 1000 x 1942 px - 72 dpi

| 64.3 kB | .png | 73.731 x 143.581 mm - 209 x 407 px - 72 dpi

| 29.8 kB | .jpg | 63.5 x 123.472 mm - 180 x 350 px - 72 dpi

Dimensional drawing basic component




ID: kaz16gi1

| 49.5 kB | .cdr |

| 8.1 kB | .png | 74.083 x 115.006 mm - 210 x 326 px - 72 dpi

| 283.3 kB | .jpg | 352.778 x 548.569 mm - 1000 x 1555 px - 72 dpi

Dimensional drawing actuator




ID: kaz16bi2

| 3.4 kB | .png | 74.083 x 45.861 mm - 210 x 130 px - 72 dpi

| 91.2 kB | .jpg | 352.778 x 217.664 mm - 1000 x 617 px - 72 dpi

Switch travel diagram




ID: kaz16si6

| 62.1 kB | .jpg | 352.778 x 150.636 mm - 1000 x 427 px - 72 dpi

| 2.3 kB | .png | 74.083 x 33.867 mm - 210 x 96 px - 72 dpi

Diagram



ID: k3o--k04

| 81.6 kB | .jpg | 352.778 x 210.961 mm - 1000 x 598 px - 72 dpi

| 3.6 kB | .jpg | 35.278 x 35.278 mm - 100 x 100 px - 72 dpi

| 3.4 kB | .png | 74.083 x 44.45 mm - 210 x 126 px - 72 dpi

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on: 24/12/2024, 7:51 am