




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.5 – 1.5 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.5 mm [.019 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.5 mm[.019 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	1 – 1.5 kgf

Dimensions

Product Length	13.5 mm[.531 in]
Compatible Insulation Diameter Range	2.79 – 4.32 mm[.11 – .17 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.5 – 1.5 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	7000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1855654-1
HDM/FA HBEMPO140T140O LM CUT

TE Part # 154897-2
.375 FLAG FASTON RECPT.

Also in the Series | FASTON 187

Crimp Terminal Housings(40)

Insertion & Extraction Tools(1)

Insulation Boots & Sleeves(1)

Joints & Splices(1)

PCB Terminals(42)

Quick Disconnects(205)

Splices(1)


Customers Also Bought




TE Part #175057-1
250 PL EX FLAG REC. 18-12AWG PTBR



TE Part #316292-5
3.2 CLUSTER REC L-TYPE TIN



TE Part #171370-3
CLUSTER BLOCK HSG PBT



TE Part #316293-1
3.2 CLUSTER BLOCK HSG NATURAL



TE Part #42563-9
250 FASTON FLAG REC 12-10 AWG NPST




TE Part #41802
250 FASTON FLAG REC 18-12 AWG TPBR



TE Part #170466-1
187 FASTON,REC.,18-14 AWG,TPBR



TE Part #170014-6
FF 110 TAB 20-16AWG PTBR



TE Part #900319-1
PL 312 FLAG REC 20-18AWG 0.32X24.9 PTPBR



TE Part #60873-1
250 FASTON FLAG REC 16-12 AWG TPBZ

Documents

Product Drawings

187 FASTON,FLAG,REC.,16-20 AWG,TPBR

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170140-2_AB_c-170140-2-ab.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170140-2_AB_c-170140-2-ab.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170140-2_AB_c-170140-2-ab.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Agency Approvals

UL Report

English