


ESK, Aluminum Electrolytic, 1,000 uF, 20%, 16 VDC, -40/+85°C, Lead Spacing = 5mm



Dimensions

D	10mm +/-0.5mm
L	15mm +2.0/-0mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	3000

General Information

Supplier:	KEMET
Series:	ESK
Dielectric:	Aluminum Electrolytic
Description:	Single Ended, Aluminum Electrolytic
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	1,000 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC, 20 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	2000 Hrs
Dissipation Factor:	16.00% 120Hz 20c
Ripple Current:	630 mAmps (120Hz 85C)
Leakage Current:	160 uA (2min 20°C)
Impedance Ratio at -25C:	5
Impedance Ratio at -40C:	6