


BAS281...BAS283

Vishay Telefunken

Small Signal Schottky Barrier Diodes

Features

- Integrated protection ring against static discharge
- Low capacitance
- Low leakage current
- Low forward voltage drop
- Very low switching time



Applications

General purpose and switching Schottky barrier diode HF–Detector Protection circuit Diode for low currents with a low supply voltage Small battery charger Power supplies DC / DC converter for notebooks

Order Instruction

Туре	Type Differentiation	Ordering Code	Remarks
BAS281	V _R = 40 V	BAS281–GS08	Tape and Reel
BAS282	V _R = 50 V	BAS282–GS08	Tape and Reel
BAS283	V _R = 60 V	BAS283–GS08	Tape and Reel

Absolute Maximum Ratings

T_i = 25°C

Parameter	Test Conditions	Туре	Symbol	Value	Unit
Reverse voltage		BAS281	V _R	40	V
		BAS282		50	
		BAS283		60	
Peak forward surge current	t _p =1s		I _{FSM}	500	mA
Repetitive peak forward current			I _{FRM}	150	mA
Forward current			۱ _F	30	mA
Junction temperature			Т _і	125	°C
Storage temperature range			T _{stg}	-65+150	°C

Maximum Thermal Resistance

T_i = 25°C

Parameter	Test Conditions	Symbol	Value	Unit
Junction ambient	on PC board 50 mmx50 mmx1.6 mm	R _{thJA}	320	K/W

Vishay Telefunken



Electrical Characteristics

 $T_i = 25^{\circ}C$

Parameter	Test Conditions	Туре	Symbol	Min	Тур	Max	Unit
Forward voltage	I _F =0.1mA		V _F			330	mV
	I _F =1mA		V _F			410	mV
	I _F =15mA		V _F			1	V
Reverse current	V _R =V _{Rmax}		I _R			200	nA
Diode capacitance	V _R =1 V, f=1MHz		CD			1.6	рF

Characteristics ($T_j = 25^{\circ}C$ unless otherwise specified)




Figure 1. Max. Reverse Power Dissipation vs. Junction Temperature




Figure 2. Reverse Current vs. Junction Temperature




Figure 3. Forward Current vs. Forward Voltage





Figure 4. Diode Capacitance vs. Reverse Voltage



BAS281...BAS283

Vishay Telefunken

Dimensions in mm



Glass case Quadro MELF / SOD80 similar to JEDEC 213 AA

96 12071

<mark>≻R3</mark> Glass



(1355)

BAS281...BAS283

Vishay Telefunken



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

1. Meet all present and future national and international statutory requirements.

2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay-Telefunken products for any unintended or unauthorized application, the buyer shall indemnify Vishay-Telefunken against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

> Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423