

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, silver, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 500

Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

Commercial data

Item number	1287510
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	BG2411
GTIN	4063151514020
Weight per piece (including packing)	405 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Device marking
Marking	
Number of individual labels	500
Number of individual labels per row	1
Identification technology	Thermal transfer for rolls

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

RoHS compliant	yes
Foil strength	175 µm
Adhesive strength	400 µm
Adhesive	Acrylic
Color	silver
Material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	> 18 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	60 mm
Length	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



Accessories

THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/in/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/in/products/5145384>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



THERMOMARK-RIBBON 110/50 - Ink ribbon

0800687

<https://www.phoenixcontact.com/in/products/0800687>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/in/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/in/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/in/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

EMLP (60X15)R SR - Label

1287510

<https://www.phoenixcontact.com/in/products/1287510>



THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/in/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in