



Figure similar

SIPLUS ET 200SP BA 2xLC-LD based on 6ES7193-6AG50-0AA0 with conformal coating, -40...+60 °C, . BusAdapter 2x LC-LD port, for single-mode optical fiber, up to max. 20 km

General information	
Product type designation	BA 2x LC-LD
based on	6ES7193-6AG50-0AA0
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch) 2x LC-LD single-mode fiber-optic cable
Supports protocol for PROFINET IO	
Number of LC ports	2; wavelength of 1 270 ... 1 380 nm, corresponds to 100BASE-LX
Cable length	
— single-mode fiber-optic cable 9/125 µm	20 km; 10 km for topology or IRT configuration; min. transmit power -15 dB, min. receiver sensitivity -28 dB
Ambient conditions	
Ambient temperature during operation	
- horizontal installation, min. - horizontal installation, max. - vertical installation, min. - vertical installation, max.	-40 °C; = Tmin (incl. condensation/frost) 60 °C; = Tmax -40 °C; = Tmin 50 °C; = Tmax
Altitude during operation relating to sea level	
- Installation altitude above sea level, max. - Ambient air temperature-barometric pressure-altitude	5 000 m Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
Relative humidity	
With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
Resistance	
Coolants and lubricants	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
— Against mechanical environmental conditions acc. to EN 60721-3-3	Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0//6AG1193-6AB00-0AA0)
Use on ships/at sea	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
— to chemically active substances according to EN	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity

60721-3-6	degree 3); *																																				
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *																																				
— Against mechanical environmental conditions acc. to EN 60721-3-6	Yes; class 6M4 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)																																				
Usage in industrial process technology																																					
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)																																				
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)																																				
Remark																																					
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!																																				
Conformal coating																																					
● Coatings for printed circuit board assemblies acc. to EN 61086	Yes; Class 2 for high reliability																																				
● Protection against fouling acc. to EN 60664-3	Yes; Type 1 protection																																				
● Military testing according to MIL-I-46058C, Amendment 7	Yes; Discoloration of coating possible during service life																																				
● Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, Class A																																				
Dimensions																																					
Width	20 mm																																				
Height	69.5 mm																																				
Depth	59 mm																																				
Weights																																					
Weight, approx.	40 g																																				
Classifications																																					
	<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>14</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-92</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-92</td></tr><tr><td>ETIM</td><td>10</td><td>EC002584</td></tr><tr><td>ETIM</td><td>9</td><td>EC002584</td></tr><tr><td>ETIM</td><td>8</td><td>EC002584</td></tr><tr><td>ETIM</td><td>7</td><td>EC002584</td></tr></table>		Version	Classification	eClass	14	27-24-26-92	eClass	12	27-24-26-92	eClass	9.1	27-24-26-92	eClass	9	27-24-26-92	eClass	8	27-24-26-92	eClass	7.1	27-24-26-92	eClass	6	27-24-26-92	ETIM	10	EC002584	ETIM	9	EC002584	ETIM	8	EC002584	ETIM	7	EC002584
	Version	Classification																																			
eClass	14	27-24-26-92																																			
eClass	12	27-24-26-92																																			
eClass	9.1	27-24-26-92																																			
eClass	9	27-24-26-92																																			
eClass	8	27-24-26-92																																			
eClass	7.1	27-24-26-92																																			
eClass	6	27-24-26-92																																			
ETIM	10	EC002584																																			
ETIM	9	EC002584																																			
ETIM	8	EC002584																																			
ETIM	7	EC002584																																			
Approvals / Certificates																																					
General Product Approval	Maritime application																																				

[Manufacturer Declaration](#)



[China RoHS](#)



last modified:

8/21/2024