

MOTION CONNECT 500

Article No. : 6FX5002-8QN21-1EJ0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data

No. of cores x cross-section mm ²	4x2,5 + 4x0,2 + 2x1,5C C
Test voltage, rms Power conductors	1.5 kV
Test voltage, rms Signal conductors	0.5 kV
Type with braking lead	Yes
Rated voltage V0/V according to EN 50395	600 V/1000 V

Mechanical data

Type of connection cable engine side	Connector SPEED-CONNECT
Connector size	1 / M23
Type of bolting	not relevant
Type of connection cable converter side	Wire ends with ferrules (OCC signal connector pre-assembled)
Maximum cable outer diameter	13.7 mm
Length	48.0 m
Weight (without connector)	13.9 kg
Static deployment	
Smallest bending radius (fixed installation)	33.2 mm
Tensile load for permanently installed cable, max.	50 N/mm ² (7252 lbf/in ²)
Torsional stress	Absolute 30°/m
Dynamic deployment	
Smallest bending radius(flexible installation in a cable carriers)	133.0 mm
Acceleration horizontal, max	2.0 m/s ²
Maximum traversing velocity	30.0 m/min
Travel path	5 m
Number of bends, max.	100,000
Tensile load for moving cable, max.	20 N/mm ² (2901 lbf/in ²)

Technical data

Ambient temperature	
Operation with permanently installed cable	-20.0 ... 80.0 °C Module-end power connector 0 ... 55°C
Operation with moving cable	0.0 ... 60.0 °C Module-end power connector 0 ... 55°C
Storage	-20.0 ... 80.0 °C Module-end power connector -20 ... 70°C
Kind of connection cable	Basis cable
Material of the cable sheath	PVC DESINA color orange RAL 2003
Type of insulation	CFC/silicone-free
Standard for behavior in fire: flame resistance	EN 60332-1-1 to 1-3
Oil resistance	EN 60811-2-1 (mineral oil only)
Verification of suitability as authorisation for USA	UL758
Verification of suitability as authorisation for Canada	CSA-C22.2-N.210.2-M90