

PRODUCT-DETAILS

# LS32P12B11

## LS32P12B11 Limit Switch



### General Information

Extended Product Type	LS32P12B11
Product ID	1SBV010312R1211
EAN	3471522615510
Catalog Description	LS32P12B11 Limit Switch
Long Description	LS32P12B11 is a 30 mm wide, standard Limit Switch made of fiber-glass reinforced UL-V0 material, with 2 mounting holes at the top, 1 ISO M16x1.5 cable entry on the bottom, steel roller plunger actuator and 1 N.O + 1 N.C snap action (Zb type) contacts

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

### Popular Downloads

Data Sheet, Technical Information	1SBC141160C0201
Instructions and Manuals	1SBC141160C0201

### Dimensions

Product Net Width	30 mm
Product Net Height	84 mm

Product Net Depth / Length	30 mm
Product Net Weight	0.067 kg

## Technical

Action Type of the Contact Element (acc. to IEC 60947-5-1)	Snap Action Simultaneous
Actuator Type	steel roller plunger
B10d Value	30 Millions operations
Conventional Free-air Thermal Current ( $I_{th}$ )	acc. to IEC 60947-5-1, $q = 40\text{ °C}$ 10 A
Degree of Protection	acc. to IEC 60529 IP65
Housing Material	Plastic
Maximum Electrical Switching Frequency	(AC-15) 3600 cycles per hour (DC-13) 3600 cycles per hour
Maximum Mounted Auxiliary Contacts	1 NO, 1 NC
Mechanical Durability	0 cycle
Mounting Type	30 mm (EN 50047)
Number and Type of Bottom Cable Glands	1 x M16x1.5 - Bottom
Pilot Duty UL/CSA	A600 Q600
Rated Impulse Withstand Voltage ( $U_{imp}$ )	6 kV
Rated Operational Current AC-15 ( $I_e$ )	(230 V AC) 3.1 A (400 V) NC 4 (24 V) 10 A (130 V) 5.5 A (240 V) 3 A
Rated Insulation Voltage ( $U_i$ )	acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 500 V acc. to UL/CSA 600 V
Rated Operational Current DC-13 ( $I_e$ )	(24 V) 6 A (110 V) 0.6 A (125 V) 0.55 A (250 V) 0.4 A
Short-Circuit Protective Devices	gG Type Fuses 10 A

## Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -30 ... +80 °C
RoHS Status	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

CQC Certificate	CQC2004010305127663
cUL Certificate	9AKK107991A7379
Declaration of Conformity - CCC	2020980305001785
Declaration of Conformity - CE	1SBD250883U1000
Declaration of Conformity - UKCA	1SBD250886U1000
Instructions and Manuals	1SBC141160C0201
RoHS Information	1SBD251097E1000

---

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	35 mm
Package Level 1 Depth / Length	32 mm
Package Level 1 Height	95 mm
Package Level 1 Gross Weight	0.077 kg
Package Level 1 EAN	3471522615510

---

## Classifications

Object Classification Code	B
ETIM 6	EC000030 - End switch
ETIM 7	EC000030 - End switch
ETIM 8	EC000030 - End switch
eClass	V11.0 : 27272601
UNSPSC	39121500

---

## Categories

Low Voltage Products and Systems → Control Products → Sensors → Limit Switches

