



fan heater (semiconductor PTC) with clip attachment 35 mm DIN standard mounting rail, 230 V AC, 150 W




Model	
product brand name	SIVACON
product designation	heater unit
design of the product	Semiconductor
General technical data	
consumed active power rated value	150 W
operating temperature	
• minimum	-45 °C
• maximum	70 °C
volume flow rate free-blowing	13.8 m³/h
Voltage	
type of voltage of the operating voltage	AC
continuous heating power at 20 °C	150 W
inrush current typical	12 A
operating voltage	
• rated value minimum	230 V
• rated value maximum	230 V
• at AC at 50 Hz rated value minimum	230 V
• at AC at 50 Hz rated value maximum	230 V
• at AC at 60 Hz rated value minimum	230 V
• at AC at 60 Hz rated value maximum	230 V
Protection class	
protection class IP	IP20
Main circuit	
operational current of the slow-blow fuse link	6.3 A
Product details	
product component	
• blower	Yes
• thermostat	No
Connections	
tightening torque with screw-type terminals maximum	0.8 N·m
type of connection technology	2-pole terminal max. 2.5 mm²
Mechanical Design	
height	75 mm
width	65 mm
depth	90 mm
fastening method	Clip for 35 mm DIN rail
mounting position	air flow direction vertical (air outlet on top)
net weight	0.3 kg
material of the enclosure	plastic

Environmental conditions

ambient temperature during storage

- minimum -45 °C
- maximum 70 °C

Approvals Certificates

General Product Approval	other	Environment
 EG-Konf.	 UR	
	Confirmation	Environmental Con- firmations

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2150-2C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2150-2C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2150-2C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

