

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, angled, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1243452
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEC
GTIN	4063151401290
Weight per piece (including packing)	189.6 g
Weight per piece (excluding packing)	189.6 g
Customs tariff number	85366990
Country of origin	DE

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter	1 mm
Litz wire cross-section	1 mm ²
Nominal current per signal contact	8 A

Signal contacts

Signal contacts max.

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

Environmental and real-life conditions

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

CA-12S1N12T0DNX - Cable connector




1243452

<https://www.phoenixcontact.com/in/products/1243452>

Drawings

Schematic diagram



Connector pin assignment

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243452>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	6 A	18	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	8 A	18	-

cULus Recognized				
------------------	--	--	--	--

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CA-12S1N12T0DNX - Cable connector



1243452

<https://www.phoenixcontact.com/in/products/1243452>

Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF



CA-12S1N12T0DNX - Cable connector



1243452


<https://www.phoenixcontact.com/in/products/1243452>

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



CA-12S1N12T0DNX - Cable connector

1243452

<https://www.phoenixcontact.com/in/products/1243452>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>

Plastic protective cap, M23, series: CA, RC, RF, UC, RM



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in