Precision Cleaners & degreasers

Features

- Removes asphalt, tar, and brake dust residues
- Eliminates squeaking of brake pads
- Does not leave any traces
- Removes brake fluid, oil, and grease
- Quick degreasing and surface preparation without chlorinated solvents

RS PRO Xbrake Cleaner

RS Stock No.: 0802719



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

XbrakeCleaner – Brake Cleaner

- *Use: Rapidly cleans and degreases brake components.*
- *Applications: Brake systems, carburettors, throttle bodies (avoid contact with engine or injection system).*
- *Surfaces: Metal components of braking systems and other mechanical parts.*

General Specifications

Package Size	500 ml
Package Type	Spray
Product Category	Cleaner & Degreaser
Appearance	Clear, Colourless Aerosol
Miscibility In Water	Insoluble
Odour	Characteristic

Mechanical Specifications

Density At 20°C	Not determined
Purity	Not determined
Water Content	N/A
Residue On Evaporation (ppm)	Not determined
Viscosity At 20°C	Not determined
Evaporation Rate	Not determined
Flammability	Flammable
Conductivity At 18°C	N/A
Specific Gravity At 20°C	Not determined

Non Volatiles	N/A
Active Content	N/A
pH	N/A
Inhalation Toxicity	May cause drowsiness or dizziness at high vapor concentrations (STOT SE 3)
VOC	volatile hydrocarbons (C7, butane, propane)
Vapour Pressure At 20°C	Not determined
KB Value	Not determined
PEL (PPM, 8 Hours TWA)	N/A
Total Shelf Life	Not determined

Operation Environment Specifications

Boiling Point	~150 °C (liquid fraction, DIN ISO 3405)
Flash Point	>41 °C (ISO 2719, liquid fraction)
Freezing Point	Not determined
Service Temperature	<50 °C