HUBER+SUHNER® DATA SHEET Between Series Adaptor: 31 N-716-50-2/133 W



Description

Adaptor jack/jack N jack (female) / 7/16 jack (female)

Low intermodulation adaptors For Test & Measurement applications

Interface standards

Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210 Series 7/16 - IEC 61169-4 CECC 22190 DIN 47223 VG 95250



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & \quad 50~\Omega \\ \text{Interface frequency max.} & \quad 7.5~\text{GHz} \end{array}$

PIM, 3rd order intermodulation

distortion (IMD) max. Static -165 dBc at 2x 43 dBm / 20 W carrier

Mechanical Data

Number of matings 500 Weight 0.0864 kg

Environmental Data

Operating Temperature -65 °C to 165 °C 2002/95/EC (RoHS) compliant

Material Data

Piece Parts Material Surface Plating

Interface - N jack (female)

Centre contact Copper Beryllium Alloy SUCOPRO Plating
Outer contact Brass SUCOPLATE (R) Plating
Body Brass SUCOPLATE (R) Plating
Insulator PFA / PTFE

Interface - 7/16 jack (female)

Centre contact Copper Beryllium Alloy SUCOPRO Plating
Outer contact Brass SUCOPLATE (R) Plating
Body Brass SUCOPLATE (R) Plating
Insulator PFA / PTFE

Related Documents

Outline drawing DOU-00014604

Ordering Information

Single package 31_N-716-50-2/133_WE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER - Excellence in Connectivity Solutions

HUBER+SUHNER
HUBER+SUHNER AG

RF Protection 9100 Herisau, Switzerland Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 47 51

Fax +41 (0)71 353 47 51 www.hubersuhner.com

Document: DOC-0000195581 O Issued: 20.02.13 Uncontrolled Copy Page 1/1