



NOTES:

1. TO BE USED WITH CRIMP MOULDINGS M22-301XX00 OR M22-302XX00.
2. SUITABLE FOR WIRE GAUGES 24-30 AWG.
3. CONTACTS SUPPLIED LOOSE IN QUANTITIES OF 100.
4. FOR HAND CRIMPING ONTO WIRE, USE HAND TOOL Z22-020 (INSTRUCTION SHEET IS-05), STRIP WIRE BY 1.0 - 1.5mm BEFORE CRIMPING.
5. RECOMMENDED CONDUCTOR CRIMP HEIGHTS:  
FOR 24 - 30AWG = 0.59±0.03mm

ORDER CODE:  
**M22-30500XX**  
FINISH:  
42 = GOLD  
46 = 100% TIN

SB	10	14.06.12	11756
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		A.LIOTTA	
CUSTOMER REF.:			
ASSEMBLY DRG:			



TOLERANCES  
 X. = ±1mm  
 X.X = ±0.25mm  
 X.XX = ±0.10mm  
 X.XXX = ±0.01mm  
 ANGLES = ±5°  
 UNLESS STATED

MATERIAL:  
 PHOSPHOR BRONZE  
 FINISH: SEE ORDER CODE  
 S/AREA: mm<sup>2</sup>

TITLE:  
 CRIMP CONTACT (LOOSE)  
 DRAWING NUMBER:  
**M22-30500XX**