



Connectors > Connector Accessories > Test Probe Receptacles



Profile Height from PCB: 5.84 mm [ .23 in ]

Funnel Entry: **Without**

Contact Mating Area Plating Material: **Tin (Sn)**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Connector & Contact Terminates To | Printed Circuit Board |
| Test Probe Hole Location          | Side Entry            |
| Connector System                  | Cable-to-Board        |
| Funnel Entry                      | Without               |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 1 |
|---------------------|---|

Contact Features

|                                      |          |
|--------------------------------------|----------|
| Contact Current Rating (Max)         | 4.75 A   |
| Contact Base Material                | Brass    |
| Contact Mating Area Plating Material | Tin (Sn) |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Dimensions

|                         |                 |
|-------------------------|-----------------|
| Profile Height from PCB | 5.84 mm[.23 in] |
|-------------------------|-----------------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -55 – 85 °C[-67 – 185 °F] |
|-----------------------------|---------------------------|



Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Product Compliance


For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-582118-0  
TEST PROBE REC130 BI BLK GPBR



TE Part # 3-582119-0  
TEST PROBE REC130 TRI-MT BLK GPBR



TE Part # 6-582118-9  
TEST PROBE REC130 BI NAT GPBR



TE Part # 3-582118-6  
TEST PROBE REC130 BI BLU GPBR





TE Part # 1-521799-5  
TEST PROBE HOUSING GREEN



TE Part # 1-521800-2  
TEST PROBE ASSEMBLY RED



TE Part # 2-582118-0  
TEST PROBE REC130L BI-MT BLK SPBR




TE Part # 1-380736-9  
TEST PROBE REC180 BI WHT GPBR




TE Part # 3-582118-9  
TEST PROBE REC130 BI WHT GPBR



TE Part # 2-582118-9  
TEST PROBE REC130 BI WHT SPBR




TE Part # 3-582118-2  
TEST PROBE REC130 BI RED GPBR



TE Part # 3-582118-4  
TEST PROBE REC130 BI YEW GPBR

Also in the Series | [Test Probe 130](#)



[Test Probe Receptacles\(17\)](#)

Customers Also Bought

TE Part #CP7312-000  
[MT2000-NO.8-0-SP](#)

Documents

[Product Drawings](#)  
[TEST PROBE HOUSING BLACK](#)

English

[CAD Files](#)  
Customer View Model  
[ENG\\_CVM\\_CVM\\_1-521799-0\\_A.2d\\_dxf.zip](#)



English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-521799-0\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-521799-0\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

**PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS**

English

**Product Specifications**

**Application Specification**

English

**Test Probe Receptacle Contacts**

English