

Impact Wrench LXT®

DTW302

18V • 3/8" • 300 Nm • 0 – 3 200 min⁻¹

Extra compact and efficient brushless impact wrench with three power settings

Variable 4-speed provides fastening control for a wide range of applications. Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge. Twin LED lights with preglow and afterglow functions for better illumination.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	80 / 130 / 180 / 300 Nm
No load speed	0 - 1000 / 1800 / 2600 / 3200 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2600 / 3400 / 4000 min ⁻¹
Drive Square	3/8 "
Tightening Capacity Standard Bolt	M10 - M20
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,8 kg
Product Dimensions (L x W x H):	138 x 81 x 246 mm
Brushless Motor	✓

User benefits

- Brushless maintenance-free and long-life motor
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Electric brake for maximum productivity and increased operator safety
- Built-in LED light illuminates the work area
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing