




Flow monitor

SIR11ABBFPKG/US-100-IPF



- 1 LED bar display
- 2 setting pushbutton
- 3 thread G1 Aseptoflex Vario



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 1	
Process connection	threaded connection G 1 external thread Aseptoflex Vario	
Application		
Special feature	Gold-plated contacts	
Application	hygienic systems	
Medium temperature	[°C] -25...95; (for SIP process: ...140 °C)	
Pressure rating	30 bar	3 MPa
MAWP (for applications according to CRN)	[bar] 30	
Electrical data		
Operating voltage	[V] 19...36 DC	
Current consumption	[mA] < 60	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time	[s] 10	
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 1	



Flow monitor

SIR11ABBFPKG/US-100-IPF

Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	20
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...100
Gases		
Setting range	[cm/s]	200...3000
Greatest sensitivity	[cm/s]	200...800
Accuracy / deviations		
Repeatability	[% of Sr]	1...5
Note on repeatability		for water 5...100 cm/s; 25 °C
		Factory setting
Temperature drift	[cm/s x 1/K]	0.1; (for water 5...100 cm/s; 10...70 °C)
Temperature gradient	[K/min]	150
Switch point accuracy	[cm/s]	± 2...± 10; (for water 5...100 cm/s; 25 °C; Factory setting)
Hysteresis	[cm/s]	2...5; (for water 5...100 cm/s; 25 °C; Factory setting)
Response times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		pushbutton
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67; IP 69K
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (55...2000 Hz)
MTTF	[years]	298

SI6600



Flow monitor

SIR11ABBFPKG/US-100-IPF

Mechanical data		
Weight	[g]	425.5
Housing		cylindrical
Dimensions	[mm]	Ø 50 / L = 119
Materials		stainless steel (316L/1.4404); PC; PBT-GF20; EPDM/X; Sealing: FKM
Materials (wetted parts)		stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4
Process connection		threaded connection G 1 external thread Aseptoflex Vario
Probe diameter	[mm]	7.7
Installation length EL	[mm]	20

Displays / operating elements		
Display	function	10 x LED, three-colour

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		



Connection

