




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **50**

Number of Rows: **2**

Features

Product Type Features

Applied Pressure	Standard
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Board-to-Board Configuration	Parallel
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	50
Number of Rows	2

Electrical Characteristics

Operating Voltage	333 VAC
Insulation Resistance	5000 MΩ

Body Features

Connector Profile	Standard
Primary Product Color	Black



Contact Features

Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Mating Square Post Dimension	.64 mm[.025 in]
	150 μin
Contact Shape & Form	Square
Contact Protection Type	Closed Entry Housing
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	2 A

Termination Features

Rectangular Termination Post & Tail Width	.69 mm[.027 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Post & Tail Length	2.92 mm[.115 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Mating Entry Location	Top
Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Stack Height	10.92 mm[.43 in]
PCB Thickness (Recommended)	1.57 mm[.055 – .094 in]
Connector Height	5.03 mm[.198 in]

Usage Conditions

Housing Temperature Rating	Standard
----------------------------	----------



Operating Temperature Range

-65 – 105 °C[-85 – 221 °F]

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	9
Packaging Method	Box, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2-102617-3 50 MODII HDR DRRA SHRD .100CL	 TE Part # 7-103166-3 50 MODII HDR DRRA SHRD LF	 TE Part # 7-146257-5 50 MODII HDR DRST B/A .100CL L	 TE Part # 2-87608-1 50 MODII HDR DRST SHRD .100CL
 TE Part # 2-828221-5 2X25P MOD2 STIFTLEI	 TE Part # 86286-1 KEYING PLUG	 TE Part # 7-102617-3 50 MODII HDR DRRA SHRD LF	

Also in the Series | Modu Connector System

 Board-to-Board Headers & Receptacles(814)	 Board-to-Board Jumpers & Shunts(5)	 Connector Hardware(4)	 PCB Headers & Receptacles(814)
---	--	---------------------------	------------------------------------

Customers Also Bought

 TE Part #6-1437622-0 KN700B1/4=KNOB BLACK KNURL 1/4	 TE Part #7-1437514-0 8134-HC-8P2=HOLTITE CONTACT 3.	 TE Part #CAT-C339-SM1 SMD Power Resistor: 7 Watt, 200-2M Ohm	 TE Part #5745988-4 09 MSFL RCPT RA 590 (IN,FM)
--	--	---	---



TE Part #1879208-1
CPF 0402 10R 0.1% 25PPM 1K RL

TE Part #5-520315-7
TRIOMATE ASSY V 7P L=3.556

TE Part #776261-1
14POS,PIN DIA 1.3,HDR ASSY,
180DEG,COD 1

TE Part #2-2176344-5
CRGCQ 1206 10K 5%

TE Part #640387-9
09P MTA156 HDR ASSY SQ R/A

Documents

Product Drawings

50 MODII VRT DR CE 100/115

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-534206-5_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-534206-5_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-534206-5_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English