

LOCTITE® SI 5927 RED™

Known as LOCTITE® 5927™
May 2014

PRODUCT DESCRIPTION

LOCTITE® SI 5927 RED™ provides the following product characteristics:

Technology	Silicone
Chemical Type	Acetoxy silicone
Appearance (uncured)	Red homogeneous paste
Components	One component - requires no mixing
Thixotropic	Reduced migration of liquid product after application to substrate
Cure	Room temperature vulcanizing (RTV)
Application	Gasketing or Sealing
Flexibility	Enhances load bearing & shock absorbing characteristics of the bond area.
Specific Application	Gasket dressing
Specific Benefit	Good temperature resistance.

LOCTITE® SI 5927 RED™ is used for gasketing and sealing applications for both plant maintenance and small, medium, and large-sized OEM. It is specially formulated to meet the low silicone volatiles requirements of the automotive industry for 315°C flange sealants. As a formed-in-place gasket/sealant, LOCTITE® SI 5927 RED™ has been designed to give outstanding performance in typical automotive gasketing applications including valve covers, rocker covers, oil pans, water pumps, end seals, intake manifolds, and rear axle housings. This product is also used as a sealant and adhesive for assembly and repair of industrial furnaces, ovens, boilers, exhaust stacks, high temperature ducting, and heating elements in electrical appliances. This product is typically used in applications up to 315 °C.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C	1.05
Odor	Acetic Acid
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

LOCTITE® SI 5927 RED™ cures on exposure to moisture in the air. The product dries tack free in 1 hour and fully cures in 24 hours. Cure times will vary with temperature, humidity and gap.

TYPICAL PROPERTIES OF CURED MATERIAL

Cured for 7 days @ 25 °C / 50% RH

Physical Properties

Shore Hardness, ISO 868, Durometer A	36
Elongation, ISO 37, %	330
Tensile Strength, ISO 37	N/mm ² 0.7 (psi) (100)

TYPICAL ENVIRONMENTAL RESISTANCE

Cured @ 25 °C / 50±5 % RH for 7 days, tested @ 25 °C, 3 mm thick film

Heat Aging

Aged at temperature indicated and tested @ 22 °C

	Week(s) @ 204 °C				
	1	2	4	8	Shore
Hardness, ISO 868, Durometer A	29	28	25	22	
Tensile Strength, ISO 527, N/mm ²	0.7	0.7	0.7	0.6	
Elongation, ISO 527-2, %	370	450	490	500	

	Week(s) @ 260 °C				
	1	2	4	7	Shore
Hardness, ISO 868, Durometer A	23	16	15	17	
Tensile Strength, ISO 527, N/mm ²	0.4	0.2	0.1	0.1	
Elongation, ISO 527-2, %	520	440	280	210	

	Week(s) @ 316 °C			
	1	2	3	
Shore Hardness, ISO 868, Durometer A	48	64	82	
Tensile Strength, ISO 527, N/mm ²	0.6	0.5	0.5	
Elongation, ISO 527-2, %	175	70	25	

At 260°C, softening is due to reversion and will occur regardless of how the sealant is cured. For flange sealing, this softening is usually an attribute.

At 315°C, hardening is due to thermal rearrangement of the polymer and also oxidation. Oxidation is retarded when the product is used as a flange sealant.

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use:

1. For best performance bond surfaces should be clean and free from grease.
2. Full performance properties will develop over 24 hours.
3. Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
4. Press or firmly clamp parts together. Do not slide parts together.
5. Excess material can be easily wiped away with non-polar solvents.
6. Excess cured material can be removed with a knife or single edge razor blade.

NOTE: Do not use LOCTITE® SI 5927 RED™ for gasketing carburetors or fuel control devices where it will be in constant contact with hydrocarbon fuels. Material will develop excessive swell and loss of mechanical properties.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our

knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.1