




FHD-MCL-42-AN

Ruland FHD-MCL-42-AN, 42mm Face Mount Shaft Collar with Drilled Hole, Anodized Aluminum, One-Piece Clamp Style, 73mm OD, 19mm Width



Description

Ruland FHD-MCL-42-AN is a one-piece shaft collar with a 42mm bore, 73mm OD, and 19mm width. FHD-MCL-42-AN has drilled holes for mounting shaft collars to sprockets, pulleys, metallic plates, or other components. Drilled holes give the user flexibility to choose inch or metric mounting hardware that best suits the application. The clamp style design does not mar the shaft, is easy to remove, and is indefinitely adjustable. Equipment manufacturers benefit from the tightly controlled face to bore perpendicularity (TIR of ? .05mm). Perpendicularity is critical for alignment when the shaft collar is used as a load bearing face, mechanical stop, or for mounting components such as gears or bearings. Proprietary processes have been developed by Ruland to maintain superior fit, finish, and holding power. FHD-MCL-42-AN is stamped with the Ruland name and bore size for ease of identification. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. FHD-MCL-42-AN is machined from solid bar stock to a fine burr free finish and sourced exclusively from North American mills. Ruland uses high grade 2024 aluminum with an anodized finish for increased screw seating torque and added corrosion resistance. It is RoHS3 and REACH compliant and manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	42 mm	Bore Tolerance	+0.050 mm / +0.012 mm
Outer Diameter (OD)	73 mm	Clearance Diameter (C) MAX	80.1 mm
Width (W)	19 mm	Width Tolerance	+0.076 mm / -0.254 mm
Hole to Center (HC)	28.75 mm	Hole to Hole (HH)	57.50 mm
Hole Diameter (H)	8.73 mm	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
Forged Clamp Screw	M8 x 25	Screw Material	18-8 300 Series Stainless Steel
Hex Wrench Size	6.0 mm	Screw Finish	Bright
Seating Torque	23 Nm	Screw Location (R)	29.49 mm
Number of Screws	1 ea	Torque Wrench	TW:BT-4C-3/8-205
Recommended Hex Key	Metric Hex Keys	Material Specification	2024-T351 Aluminum Bar
Temperature	-40°F to 200°F (-40°C to 93°C)	Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.314821	UPC	63452937725
Tariff Code	8483.60.8000	UNSPC	31162811
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 2	No backslot		
Prop 65	WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		