




Switches > Switch Knobs



Primary Product Material: Phenolic

Knob Design: Ribbed

Shaft Size: 6.35 mm [.25 in]

Product Diameter: 34.8 mm [1.37 in]

Primary Product Color: Black

Features

Configuration Features

Spinner	Without
Skirt	Without
Spin Plate	Without
Knob Design	Ribbed

Body Features

Primary Product Material	Phenolic
Primary Product Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Product Diameter	34.8 mm[1.37 in]

Identification Marking

Indicator Style	White Square
Indicator Location	Top



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Alcoswitch PKX



Switch Knobs(3)

Customers Also Bought




TE Part #1757820-7
AMPLIMITE,ASY,RCPT,STD,109,ZN,2,CT




TE Part #1546413-3
ETHERNET RJ-45 BLKHD PASSTHRU




TE Part #1-1393117-9
KUP-11A15-120=KU



TE Part #3-641216-6
06P MTA100 HDR ASSY FL/RA LF



TE Part #1-643075-0
10P MTA100 MOLDED COVER



TE Part #2-520184-4
ULTRAFast 250 ASSY REC 22-18 TPBR LP



TE Part #36932
BODY SOLIS RING 4/0 3/8



TE Part #3-641237-2
02P MTA100 CONN ASSY RED 30AU



TE Part #640250-3
03P SL156 HSG W/LCK RAMP NATL



TE Part #1-6609037-6
30EMC6=F8131

Documents

Product Drawings

PKX110B1/4=KNOB BLACK MATTI

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1437625-2_J.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_1-1437625-2_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1437625-2_J.3d_igs.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English