



**Part Number :** [732860070](#)

**Product Description :** Bolt-in EMI Filter Plate,  
Standard Density, 2x3, Straight, 10 pF Insulated,  
26.92mm Plate Length

**Series Number :** 73286

**Status :** Active

**Product Category :** EMI Filter Plates



---

## Documents & Resources

### Drawings

[732860070 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	EMI Filter Plates
Series	73286
Description	Bolt-in EMI Filter Plate, Standard Density, 2x3, Straight, 10 pF Insulated, 26.92mm Plate Length
Application	RF
Product Name	Bolt-in EMI Filter Plates
Type	Bolt-in Standard Density
UPC	198282678854

**Electrical**

Current - Maximum per Contact	5.0A
Capacitance Value	10 pF
Capacitance Tolerance	max.
3 dB Cut-off Frequency Max. (MHz)	635
Dielectric Withstanding Voltage (V)	250
EMI Filter Circuits	Insulated
Voltage - Maximum	100V DC

**Physical**

Circuits (Loaded)	6
Length	26.92mm
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Number of Rows	2

Number of Lines per Row	3
Orientation	Straight
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm

---

This document was generated on Oct 02, 2025