



Main

| | |
|---------------------------|------------------------------|
| Range of product | NSX100...250 |
| Range | ComPact |
| Device short name | CT module and voltage output |
| Product or component type | Current transformer |
| Device application | Control |
| Range compatibility | ComPact NSX circuit breaker |
| Poles description | 3P |
| Network type | AC |
| [In] rated current | 250 A 1.1 VA |

Complementary

| | |
|--------------------------------|-------------------------------------|
| [Ue] rated operational voltage | 530 V |
| Network frequency | 50/60 Hz |
| Current transformer ratio | 250/5 A |
| Auxiliary connection terminal | Cable connector 2.5 mm ² |

Environment

| | |
|-----------------------------------|------------------------------|
| Electrical shock protection class | Class II |
| IP degree of protection | IP40 conforming to IEC 60529 |
| IK degree of protection | IK04 conforming to IEC 62262 |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 991 g |
| Package 2 Weight | 4.451 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.