




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VDC
-------------------	--------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.3 µm[11.81 µin]
Mating Tab Width	.7 mm[.028 in]
PCB Contact Termination Area Plating Material Thickness	2 µm[78.74 µin]
Contact Layout	Inline
Contact Base Material	Brass
Mating Tab Thickness	.5 mm[.02 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Tab
Contact Current Rating (Max)	3 A

Termination Features

Termination Post & Tail Length	2.8 mm, 16.8 mm[.11 in][.661 in]
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Width	7 mm[.27 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	11.3 mm[.444 in]



Connector Length	10 mm[.39 in]
------------------	---------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	900
Packaging Method	Tape

Product Compliance

For compliance documentation, visit the product page on TE.com>












EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 5-1747072-5 GRACE INERTIA CONN 2.5 ON TAPE HDR 5P NA	 TE Part # 5-1747072-2 GRACE INERTIA CONN 2.5 ON TAPE HDR 2P NA	 TE Part # CAT-G7534A-C1701 STD Temp Sig GRACE INERTIA Cap	 TE Part # 1903392-1 GIC 2.5 W CAP HSG 3P NATURAL
 TE Part # 6-1747072-2 GRACE INERTIA CONN 2.5 ON TAPE HDR 2P RE	 TE Part # 5-1747511-1 GRACE INERTIA CONN 2.5 ON TAPE HDR 3/5P	 TE Part # 5-1747072-6 GRACE INERTIA CONN 2.5 ON TAPE HDR 6P NA	 TE Part # 6-1747072-4 GRACE INERTIA CONN 2.5 ON TAPE HDR 4P RE
 TE Part # 7-1747072-2 GRACE INERTIA CONN 2.5 ON TAPE HDR 2P BL	 TE Part # 7-1747072-4 GRACE INERTIA CONN 2.5 ON TAPE HDR 4P BL	 TE Part # 5-1747072-4 GRACE INERTIA CONN 2.5 ON TAPE HDR 4P NA	 TE Part # 7-1747511-1 GIC 2.5 ON TAPE HDR 3/5P BLUE

Also in the Series | GRACE INERTIA 2.5

 Connector Contacts(6)	 Connector Hardware(7)	 PCB Headers & Receptacles(173)	 Power Contacts(2)
 Rectangular Power Connectors(11)	 Wire-to-Board Connector Assemblies & Housings(36)	 Wire-to-Board Headers & Receptacles (173)	



Customers Also Bought



TE Part #1892714-2
MBXL R/A HDR 2P




TE Part #7-1747072-4
GRACE INERTIA CONN 2.5 ON TAPE HDR 4P BL




TE Part #OCX24688-FNM
TRI-BAND, OMNIDIRECTIONAL ARRAY



TE Part #2-1419108-4
RTB14005F




TE Part #1903392-1
GIC 2.5 W CAP HSG 3P NATURAL



TE Part #4-2176377-0
RQ 0805 340K 0.1% 10PPM 1K RL




TE Part #1747049-1
GRACE INERTIA CONNECTOR 6.5 3POS HEADER



TE Part #2134384-1
GIC 2.5 REC CONT TIN PLATE TYPE (2L TYPE



TE Part #1747591-1
GRACE INERTIA CONN 2.5 REC CONTACT



TE Part #6-1747072-3
GRACE INERTIA CONN 2.5 ON TAPE HDR 3P RE

Documents

Product Drawings

GRACE INERTIA CONN 2.5 ON TAPE HDR 3P NA

Japanese

CAD Files

Customer View Model

ENG_CVM_CVM_5-1747072-3_G.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1747072-3_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1747072-3_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Application Specification

Japanese