



Eliwell France
 310 boulevard Charles de Gaulle
 92390 Villeneuve la Garenne - France
 tel: +33 (0)1 41 47 71 71
 fax: +33 (0)1 47 99 95 95

Product Datasheet



ID 970

Single stage controller for temperature

The ID 970 controllers are devices suitable for applications on normal or low temperature refrigerating units. They are provided with a PTC thermostatic probe input (NTC can be selected by parameter) and two relay outputs for compressor and defrost management. Defrost cycles can be controlled at time intervals. The value of the probe's reading is viewed on a display by three digits and a minus sign; the decimal point reading can be set by parameter. All the versions are provided with a TTL connection in order to use Copy Card, the quick programming accessory. In addition, the 16 A compressor relay options and the buzzer are provided. These controllers are available in the 32x74 standard format and the power supply voltage is, on choice, 230 Va or 12 Va/c.

Technical Data

Frontal protection	IP 65
Container	plastic resin PC+ABS UL94V-0
Dimensions	32x74 mm, depth 60 mm
Mouting	panel mounting, cut out 29x71 mm (+0.2/- 0.1mm)
Usage temperature	-5...55°C
Storage temperature	-30...85°C
Usage environment humidity	10...90% RH
Storage environment humidity	10...90% RH
Display	3½ digits plus sign
Precision	above 0.5% of bottom scale + 1 digit
Consumption	3 VA
Resolution	1°C or 0.1°C (selectable with a parameter).
Power supply	230Vac, 12Vac/cc ± 15%, 50/60Hz



The continuous improvement of our products can cause some variations in this document even without notice.