

CA-19S1N128007X - Cable connector



1243750

<https://www.phoenixcontact.com/in/products/1243750>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos. : 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 6 mm ... 10 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1243750
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEA
GTIN	4063151402723
Weight per piece (including packing)	95.2 g
Weight per piece (excluding packing)	91.9 g
Customs tariff number	85366990
Country of origin	DE

CA-19S1N128007X - Cable connector



1243750

<https://www.phoenixcontact.com/in/products/1243750>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Coding	N
Insulation body material	PA 6.6
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Contact diameter	1.5 mm
Litz wire cross-section	0.08 mm ²
Litz wire cross-section	1 mm ²
Rated current	10 A
Rated voltage	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter	1 mm
Litz wire cross-section	0.08 mm ²
Litz wire cross-section	1 mm ²
Nominal current per signal contact	8 A

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67

CA-19S1N128007X - Cable connector



1243750

<https://www.phoenixcontact.com/in/products/1243750>

Thread type	M23
-------------	-----

Seal

External cable diameter	6 mm ... 10 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-19S1N128007X - Cable connector


1243750

<https://www.phoenixcontact.com/in/products/1243750>



Drawings

Schematic diagram



Connector pin assignment

CA-19S1N128007X - Cable connector





1243750

<https://www.phoenixcontact.com/in/products/1243750>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243750>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	6 A	18	-
Signal	48 V	5 A	18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	10 A	18	-
Signal	48 V	8 A	18	-

cULus Recognized				
-------------------------	--	--	--	--

CA-19S1N128007X - Cable connector



1243750

<https://www.phoenixcontact.com/in/products/1243750>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

CA-19S1N128007X - Cable connector



1243750

<https://www.phoenixcontact.com/in/products/1243750>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CA-19S1N128007X - Cable connector

1243750

<https://www.phoenixcontact.com/in/products/1243750>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF



CA-19S1N128007X - Cable connector

1243750

<https://www.phoenixcontact.com/in/products/1243750>




RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



CA-19S1N128007X - Cable connector

1243750

<https://www.phoenixcontact.com/in/products/1243750>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



RF-Z0003X - Square mounting flange

1242369

<https://www.phoenixcontact.com/in/products/1242369>



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

CA-19S1N128007X - Cable connector

1243750

<https://www.phoenixcontact.com/in/products/1243750>



CA-Z0077X - Metal protective cap

1245447

<https://www.phoenixcontact.com/in/products/1245447>



Metal protective cap, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>



Plastic protective cap, M23, series: CA, RC, RF, UC, RM

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in