



Connectors > Pluggable IO Connectors & Cages > zSFP+ Stacked Cage Assembly: Gasket



Form Factor: **zSFP+ Stacked (SFP28)**

Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.8 mm [ .032 in ]**

Sealable: **Yes**

Circuit Application: **Signal**

[All zSFP+ Stacked Cage Assembly: Gasket \(34\)](#)

Features

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP28)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	Yes

Configuration Features

Lightpipe Style	Standard
Number of Positions	480
Number of Ports	24
Port Matrix Configuration	2 x 12

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Contact Features

Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
--------------------------------------	--



Tail Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Housing Features

Cage Material	Nickel Silver Alloy
Centerline (Pitch)	.8 mm[.032 in]

Usage Conditions

Operating Temperature Range	0 – 70 °C[32 – 158 °F]
-----------------------------	------------------------

Operation/Application

Pluggable I/O Applications	zSFP+ Thermally Enhanced
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>












EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 <p>TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG</p>	 <p>TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG</p>	 <p>TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG</p>	 <p>TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG</p>
 <p>TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG</p>	 <p>TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG</p>	 <p>TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG</p>	 <p>TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG</p>
 <p>TE Part # CAT-C11-N490111 SFP28 to SFP28 Cable Assembly: 28 AWG</p>	 <p>TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG</p>	 <p>TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG</p>	

Customers Also Bought







TE Part #1734375-1  
CHAMP .050 HIGH RISE, REVERSED




TE Part #5-1375870-4  
RCPT ASSY, 12 POS, VERT, 0.8MM MI




TE Part #2132529-3  
IMP100S, H, V3P6C, LG, REW39, 5.5




TE Part #2349202-5  
SFP56 STACKED 2X1 RECEPTACLE ASSEMBLY




TE Part #1934949-1  
Tinman 5pr 8col vert rcpt 15mm stack




TE Part #1734100-3  
Champ050 series, 30pos, Au over PdNi




TE Part #1-1871058-5  
PCI EXPRESS CONN. EON TYPE, 280P, L=3.25



TE Part #1734101-3  
Champ050 series, 30pos, Au over PdNi



TE Part #6-2213362-2  
RCPT ASSY, DIMMABLE PHOTOCONTROL, 150C, 3 P



TE Part #2007808-2  
IMP100S, H, V4P10C, LG, OE46, 4.9

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2227838-8\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2227838-8\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2227838-8\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English