

# Product datasheet

Specifications



servo motor MH3 100 3,3Nm,no key,single 16 lines,no brake,IP65/IP67,4kRPM

MH31001P06A2200

Discontinued on: 9 Feb 2023

Discontinued

EAN Code: 3606485395821

## Main

Range compatibility PacDrive 3

Device short name MH3

Product or component type Servo motor

## Complementary

Maximum mechanical speed 6000 rpm

[Us] rated supply voltage 115...480 V

Network number of phases Three phase

Continuous stall current 3.15 A

Continuous stall torque 3.4 N.m, 115...480 V, three phase

Continuous power 1520 W

Peak stall torque 10.8 N.m, 115...480 V, three phase

Nominal output power  
0.35 W, 115 V  
0.67 W, 230 V  
1.26 W, 400 V  
1.52 W, 480 V

Nominal torque  
3.3 N.m for LXM52 at 3.07 mA, 115 V, three phase  
3.2 N.m for LXM52 at 2.99 mA, 230 V, single phase  
3 N.m for LXM52 at 2.83 mA, 400 V, three phase  
2.9 N.m for LXM52 at 2.75 mA, 480 V, three phase  
3.3 N.m for LXM62 at 3.07 mA, 115 V, single phase  
3.2 N.m for LXM62 at 2.99 mA, 230 V, single phase  
3 N.m for LXM62 at 2.83 mA, 400 V, three phase  
2.9 N.m for LXM62 at 2.75 mA, 480 V, three phase

Nominal speed  
1000 rpm for LXM52 at 3.07 mA, 115 V, single phase  
2000 rpm for LXM52 at 2.99 mA, 230 V, single phase  
4000 rpm for LXM52 at 2.83 mA, 400 V, three phase  
5000 rpm for LXM52 at 2.75 mA, 480 V, three phase  
1000 rpm for LXM62 at 3.07 mA, 115 V, single phase  
2000 rpm for LXM62 at 2.99 mA, 230 V, single phase  
4000 rpm for LXM62 at 2.83 mA, 400 V, three phase  
5000 rpm for LXM62 at 2.75 mA, 480 V, three phase

Maximum current Irms 11.2 A

Shaft end Smooth shaft

Second shaft Without second shaft end

Shaft diameter 19 mm

Shaft length 40 mm

IP degree of protection IP65 standard

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Encoder type	Single turn SinCos Hiperface
Speed feedback resolution	16 periods
Holding brake	Without
Mounting support	International standard flange
Motor flange size	100 mm
Electrical connection	Rotatable right-angled connectors
Torque constant	1.08 N.m/A at 120 °C
Back emf constant	70.3 V/krpm
Number of motor poles	5.0
Rotor inertia	3.19 kg.cm <sup>2</sup>
Stator resistance	4.12 Ohm
Stator inductance	14.9 mH
Stator electrical time constant	4.5 ms
Maximum radial force Fr	900 N at 1000 rpm 720 N at 2000 rpm 630 N at 3000 rpm 570 N at 4000 rpm 530 N at 5000 rpm
type of cooling	Natural convection
Length	128.6 mm
Centring collar diameter	95 mm
centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	3.34 kg
Sizing reference	MH31001P
Temperature copper hot	135 °C
compatible drive output current 3s peak 2	15 A

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	18.0 cm
Package 1 Length	35.6 cm
Package 1 Weight	4.04 kg

## Contractual warranty

Warranty	18 months
----------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	<b>1437</b>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	<a href="#">REACH Declaration</a>
PVC free	Yes

## Use Again

### Repack and remanufacture

Circularity Profile	<b>No need of specific recycling operations</b>
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins