

Product type designation

SCALANCE XB004-1

SCALANCE XB004-1 UNMANAGED INDUSTRIAL ETHERNET SWITCH FOR 10/100MBIT/S; WITH 4 X 10/100MBIT/S TWISTED PAIR- PORTS WITH RJ45-SOCKETS; 1 X100MBIT/S MULTIMODE GLASS FOC-PORT WITH SC-SOCKET; FOR CONFIGURING SMALL STAR- AND LINE TOPOGRAPHIES; LED-DIAGNOSIS, IP20, 24 V DC POWER SUPPLY, MANUAL AVAILABLE AS DOWNLOAD



Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s
---------------	-----------------------

Interfaces / for communication / integrated

Number of electrical connections	4; RJ45
<ul style="list-style-type: none"> for network components or terminal equipment 	
Number of 100 Mbit/s SC ports	1
<ul style="list-style-type: none"> for multimode 	
Number of 1000 Mbit/s LC ports	0
<ul style="list-style-type: none"> for multimode 	
<ul style="list-style-type: none"> for single mode (LD) 	

Interfaces / others

Number of electrical connections	1
<ul style="list-style-type: none"> for power supply 	
Type of electrical connection	3-pole terminal block
<ul style="list-style-type: none"> for power supply 	

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	AC/DC
---	-------

Supply voltage	
<ul style="list-style-type: none"> external 	24 V
<ul style="list-style-type: none"> external 	19.2 ... 28.8 V
<ul style="list-style-type: none"> at AC 	24 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	0.6 A / 60 V
Consumed current / maximum	0.11 A
Power loss [W]	
<ul style="list-style-type: none"> at DC / at 24 V 	2.64 W

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	-10 ... +60 °C
<ul style="list-style-type: none"> during storage 	-40 ... +80 °C
<ul style="list-style-type: none"> during transport 	-40 ... +80 °C
Relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20

Design, dimensions and weight

Design	Box
Width	45 mm
Height	100 mm
Depth	87 mm
Net weight	0.165 kg
Mounting type	
<ul style="list-style-type: none"> 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> wall mounting 	Yes
<ul style="list-style-type: none"> S7-1500 rail mounting 	No

Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> multiport mirroring 	No
<ul style="list-style-type: none"> CoS 	Yes
<ul style="list-style-type: none"> switch-managed 	No

Product functions / Redundancy

Product function	
<ul style="list-style-type: none"> Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No

Standards, specifications, approvals

Standard	
----------	--

<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0:2009, EN60079-15:2010, II 3 G Ex nA IIC T4 Gc, KEMA 07ATEX0145 X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2
Certificate of suitability / CE marking	Yes
<ul style="list-style-type: none"> • Certificate of suitability 	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • Certificate of suitability / C-Tick 	Yes
<ul style="list-style-type: none"> • Certificate of suitability / KC approval 	Yes
MTBF / at 40 °C	232 y

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com

Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)</p>
----------------------	--

last modified:

15.02.2016