

Article No. : 1FL2205-2AF11-1MB0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	Medium Inertia
Static torque	3.60 Nm
Static current	2.90 A
Maximum torque	11.50 Nm
Maximum current	9.5 A
Maximum speed	6,000 rpm
Rotor moment of inertia	3.1500 kgcm ²
Weight	4.7 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	3,000 rpm
Rated torque	3.00 Nm
Rated current	2.5 A
Rated power	0.94 kW

Encoder system	
Encoder system	Absolute encoder 21-bit singleturn + 12-bit multiturn

Motor connection	
Connection type	Metal angular connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	48
Flange size (AB)	95 mm
Centering ring (N)	80 mm
Hole circle (M)	100 mm
Screw-on hole (S)	6.6 mm
Overall length (LB)	178.9 mm
Diameter of shaft (D)	19 mm
Length of shaft (E)	40 mm
Length of flange diagonal (P)	120 mm
Shaft end	Shaft with parallel key (half-key balancing)
Color of the housing	Anthracite RAL 7016



Holding brake	
Rated voltage	24 V DC 10 %
Rated current	0.57 A
Holding torque M _{4Br}	8.00 Nm
Opening time	90 ms
Closing time	25 ms