


DATA SHEET




Nickel-Metal Hydride Battery			Size : AA
Capacity ¹⁾	Nominal		2570mAh
	Minimum		2450mAh
Nominal Voltage			1.2V
Charging Current x Time		Fast Charge ²⁾	2500mA × 1.1h
Ambient Temp.	Charge Condition	Fast Charge ²⁾	0°C - 40°C
		Discharge Condition	
	Storage Condition	Less than 90days	-20°C - 40°C
		Less than 1year	-20°C - 30°C
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)			Approx. 25mΩ (at 1000Hz)
Weight ⁴⁾			Approx.30g
Size ⁴⁾ : (Diameter) x (Height)			14.5(D) x 50.4(H) mm

- 1)Single cell capacity under the following condition.
 Charge : 250mA×16h, Discharge : 500mA(E.V.=1.0V) at 20°C
 2)Use recommended charging system.
 3)After a few charge and discharge cycles under the above 1) condition.
 4)With tube.

Typical Characteristics

Charge



Discharge

