



Main

Range	Thalassa
Product or component type	Enclosure
Device short name	PLD
Enclosure type	DIN enclosure Distribution enclosure
Enclosure nominal height	850 mm
Enclosure nominal width	465 mm
Enclosure nominal depth	320 mm
Enclosure mounting	Floor-standing
Product compatibility	Fuse Size DIN: 00

Complementary

Device composition	1 x top part 1 x bottom part 2 x side part 1 x rear panel 1 x key lock 1 x door
Body type	Sealed top and open bottom part assembled with side parts
Door type	Plain front
Number of doors	1
Door opening	Reversible - opening angle > 180 °
Lock type	Key lock
Key number	1242 E
Accessibility for operation	Front Bottom
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7032

Environment

standards	IEC 62208
IP degree of protection	IP43 : plinth type open bottom conforming to IEC 60529 IP54 : with additional sealing kit conforming to IEC 60529
IK degree of protection	IK10 plain door conforming to IEC 62262
fire resistance	960 °C conforming to IEC 62208
ambient air temperature for storage	-35...90 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations