

# Eaton 135697

Catalog Number: 135697

Eaton Moeller® series E58 Thru-beam photoelectric sensor, transmitter, Sn=250m, 4L, 10-30VDC, NPN, PNP, M30, metal, M12

### General specifications



Product Name	Catalog Number
Eaton Moeller® series E58 Thru-beam photoelectric sensor	135697

EAN  
4015081324903

Product Length/Depth  
228.6 mm

Product Height  
44.45 mm

Product Width  
165.1 mm

Product Weight  
0.2 kg

### Certifications

CSA-C22.2 No. 14  
UL Category Control No.: NRKH, NRKH7

Certified by UL for use in Canada  
CSA File No.: UL report applies to both  
US and Canada  
IEC/EN 60947-5-2  
UL File No.: E166051  
CE  
UL  
UL 508

## Product specifications

### Type

Optical sensors

### Device type

Transmitter

### Electric connection type

Plug-in connection

### Fitted with:

Transmitter (for combination with detector)

### Enclosure material

Metal

### Enclosure type

Cylinder, screw-thread

### Explosion safety category for dust

None

### Explosion safety category for gas

None

### Functions

Short-circuit protection

Protection against polarity reversal

Thru-light beam

Protection against wire breakage

### Voltage type

DC

### Wire size

0

### Connection type

Plug-in connection M12 x 1

4-wire

### Cable sheath material

Polyvinyl chloride (PVC)

### Light type

Other

### Degree of protection

NEMA 4

IP68

### Interface type

## Resources

### Catalogs

Product Range Catalog Sensors – products, basic information, applications

### Declarations of conformity

DA-DC-00004657.pdf

DA-DC-00004652.pdf

### Drawings

eaton-proximity-switches-e58-diffuse-reflective-sensor-dimensions-002.eps

eaton-proximity-switches-e58-3d-drawing.eps

### Installation instructions

IL05305003Z

Other

#### LED indicator

Status indication of Operating voltage: Red LED

#### Switch function type

Other

#### Load current

Max. 100 mA (I<sub>e</sub>)

#### Laser protection class

None

#### Operation agent-safety class

Safety class 2

#### Shock resistance

100 g, Mechanical, Shock duration 3 ms

#### Optical surface material

Glass

#### Output current (mA) - max

100 mA

#### Output current at protected output - max

0 mA

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - max

30 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - min

10 V

#### Rated switching distance (S<sub>n</sub>)

250000 mm

#### Reflector distance - min

0 mm

#### Sensor height

0 mm

Sensor length

111 mm

Switching distance - max

0 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

312 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP

Sensor material

Stainless steel

Wavelength of the sensor

0 nm

Width sensor

0 mm

Product category

E58 Harsh Duty Series

Response time

1 ms

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

30 mm

Light dot size

0 mm<sup>2</sup>

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

0

Opening angle

0 °

Adjustment type

Other



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia