

## Aluminium oxide mounted flap wheel F dia. 20x10 mm shank dia. 6 mm A80 for fine grinding & finishing



**Aluminium oxide mounted flap wheel F dia. 20x10 mm shank dia. 6 mm A80 for fine grinding & finishing**

Item number: [44400086](#)

EAN: [4007220292594](#)

On mounted flap wheels, the flaps made of coated abrasive are arranged radially around the tool axis in a fan-type structure. Their flexibility enables them to adapt perfectly to the contours of the workpiece. The abrasive grain is embedded in the sturdy, flexible cloth backing material by means of a resinoid bond.

In ISO 3919, mounted flap wheels are designated as "flap wheels with shaft".

For general applications from coarse to fine grinding.

---

### Technical information

Abrasive	Aluminium oxide A
Dia. external	20 mm
Dia. shank	6 mm
Grit size	80
Length, shank	40
Max. RPM	38100 RPM
RPM, optimum	19000 RPM
Width	10 mm

---

## Advantages

- ✔ Highly flexible, enabling optimal adjustment to the contour.
- ✔ Consistently high stock removal rate over the entire tool life as new, aggressive abrasive is constantly exposed.
- ✔ Can be used face-down very close to edges and in corners thanks to the flat, moulded-core design.

---

## Recommendations for use

- ✔ Reducing the contact pressure and the peripheral speed and adding grinding oil diminishes tool wear and thermal load on the workpiece.
  - ✔ To increase the stock removal rate, it is advisable to use a coarser type of grit instead of increasing the contact pressure. This will prevent unnecessary tool wear and thermal load on the workpiece.
  - ✔ The increase in cutting speed leads to a slightly finer surface quality. Increasing the contact pressure makes the surface slightly coarser. The softer the material that is being worked on, the coarser the surface (when using the same grit size).
  - ✔ For the best results, use at a recommended cutting speed of 15-20 m/s. This provides an ideal compromise between stock removal rate, surface quality, thermal load on the workpiece and tool wear.
  - ✔ Use grinding oil that is suitable for the material in order to significantly increase the tool life and the abrasive performance of the tools.
-

## Safety notes

- ✓ For safety reasons, the maximum permitted rotational speed indicated must never be exceeded.
- ✓ The contact pressure must be significantly reduced if the specified optimum rotational speed is exceeded.
- ✓ Safety can only be guaranteed if the clamping length is at least 15 mm and the specified maximum rotational speed is not exceeded with unsupported shank lengths.

---

## Materials that can be worked

- ✓ Aluminium
- ✓ Annealed cast iron
- ✓ Brass
- ✓ Cast steel
- ✓ Copper
- ✓ Grey/nodular cast iron (GG/GJL, GGG/GJS)
- ✓ Hardened, heat-treated steels over 1.200 N/mm<sup>2</sup> (< 38 HRC)
- ✓ Stainless steel (INOX)
- ✓ Steel materials with a hardness > 54 HRC
- ✓ Steels up to 1,200 N/mm<sup>2</sup> (< 38 HRC)

---

## Applications

- ✓ Deburring
  - ✓ Leveling
  - ✓ Step-by-step fine grinding
  - ✓ Structuring (matt finishing, brush matting and satin finishing)
  - ✓ Surface work
  - ✓ Work on weld seams
-

## Drive types

- ✔ Drive spindle
  - ✔ Flexible shaft drive
  - ✔ Straight grinder
- 



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)