



Chemical protection

ULTRANITRIL 358

Frequent contact | ultra-comfort wear



ADVANCED GRIP
TECHNOLOGY

CHEMICAL PROTECTION
TYPE A



3111A



TYPE A
AJKOPT



EN ISO 374-5



X1XXXX



ISO 18889



CATEGORY 3

0334

ISO 13997:

4.9 N

DEXTERITY

EN ISO 21420:
5/5

Designed with an embedded optimal grip to safely handle tasks in dry & greasy environments

SPECIFIC ADVANTAGES



Thermal protection

- Added comfort and thermal insulation, due to the cotton-knit lining



Comfort

- Very supple glove providing high dexterity
- Good fingertips sensitivity



Productivity

- Optimal grip to improve productivity, reduce hand fatigue and enhance safety



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Plastic packaging optimized
- Recycled material in the packaging: 30 %

INDUSTRIES

- Automotive/mechanical industry
- Chemical industry
- Petrochemical industry
- Cosmetics and Pharmaceutical industry
- Agriculture sector

APPLICATIONS

- Spray mixtures preparation
- Pesticides handling
- Tank filling
- Application & spreading of pesticides
- Pesticides waste management
- Treatment equipment cleaning
- Maintenance in wet environments (water, oil, greases, hydrocarbons)
- Chemical product blending
- Handling drums of chemical products
- Maintenance and handling



Chemical protection

ULTRANITRIL 358

Frequent contact | ultra-comfort wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
3 1 1 1 A	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance

EN407	THERMAL RISKS (HEAT AND FIRE)
	PERFORMANCE LEVELS (X = NOT TESTED)
X 1 X X X X	
0-4 0-4 0-4 0-4 0-4 0-4	
	Resistance to large quantities of molten metal
	Small splashes of molten metal
	Radiant heat resistant
	Convective heat resistance
	Contact heat resistance
	Limited flame spread

EN ISO 374-1	CHEMICAL RISKS
	A: Methanol J: n-Heptane K: Sodium hydroxide 40% O: Ammonia 25% P: Hydrogen peroxide 30% T: Formaldehyde 37%
TYPE A	

	PROTECTION FROM PESTICIDES
G2	G2: Diluted & concentrated pesticides / Mechanical risk
ISO 18889	

EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Textile support Mapa Technology
Exterior finish	Reinforced grip
Material	Nitrile
Colour.s	Green
Length (cm)	36
Thickness (mm)	1,1
European sizes	6 7 8 9 10 11

LOGISTIC DETAILS

Packaging	12 pairs/bag 72 pairs/carton
-----------	---------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/05/24/1139
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France