



FLAMESTAT TROUSERS 2144 ATHS

ART. NO: 121354

Dirt, oil and water repellent / Concealed front button / 2 front pockets / 2 back pockets with flap / D-ring at waistband / Double reinforced crotch seam / Leg pocket with flap and concealed snap fastening, mobile phone pocket and loop for ID-card holder / Leg pocket with flap and inside folding rule pocket / Pre-shaped knees / CORDURA®-reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / Adjustable leg length with 5 cm hem allowance / Approved according to EN 14404 together with kneepads 124292, EN 61482-1-2 APC 1, EN 61482-1-1 ELIM 9 cal/cm² (see Electric arc table for certified garment combinations for EN 61482-1-2 class 2 and open arc according to EN 61482-1-1), EN ISO 11612 A1 A2 B1 C1 E2 F1, EN ISO 11611 A1 A2 class 1 (see Flame and welding table for certified garment combinations), EN 1149-5 and EN 13034 Type PB [6] / Certified after 50 washes / Leasing-laundry tested according to ISO 15797 / OEKO-TEX® certified.

Material: 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre. Reinforcement: 79% cotton FR, 20% polyamide, 1% anti-static fibre. Inherent flame protection. In transition to PFAS free.

Weight: 300 g/m².

Color: F540 Navy

Size: Regular: C44-C62 Short: D84-D116



PRO

CORDURA®
FABRIC



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04