

Product datasheet

Specifications



Acti9 iC60H RCBO plug on neutral - 1P+N_s - 25A - C - 10000A - 100mA - type A

Local distributor code:
405638789A9D06825

EAN Code: 3606481369154

Main

Circuit breaker application	Distribution
Range	Acti9
product name	Acti9 iC60 RCBO
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	iC60H RCBO PoN
Poles description	1P + N _s
[In] rated current	25 A at 50 °C
Earthing system	TN
Curve code	C
Earth-leakage sensitivity	100 mA
Breaking capacity	10000 A I _{cn} at 240 V AC 50/60 Hz conforming to IEC 61009-2-2

Complementary

Neutral position	Left
Number of protected poles	1
Device location in system	Outgoer
Network frequency	50/60 Hz
Network type	AC
Trip unit technology	Thermal-magnetic
Magnetic tripping limit	5...10 x I _n
[U _e] rated operational voltage	230/240 V AC 50/60 Hz
Residual current tripping technology	Voltage dependent
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
[I _{cs}] rated service breaking capacity	7500 A at 240 V AC 50/60 Hz conforming to IEC 61009-2-2
Electrical insulation class	Class II
Limitation class	3
[U _i] rated insulation voltage	400 V AC 50/60 Hz
[U _{imp}] rated impulse withstand voltage	4 kV
Surge current	250 A
Suitability for isolation	Yes

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contact position indicator	Yes
control type	Toggle
Local signalling	ON/OFF indication Fault indication
Mounting mode	Plug-on
Mounting support	Isobar B Isobar A
Comb busbar and distribution block compatibility	NO
9 mm pitches	2
Height	110 mm
Width	18 mm
Depth	72 mm
Net weight	156 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	5000 cycles
Locking options description	Padlock in on or off position
Connections - terminals	Screw clamp terminal (top) 1...16 mm² flexible Screw clamp terminal (bottom) 1...10 mm² flexible Screw clamp terminal (top) 1...25 mm² rigid Screw clamp terminal (bottom) 1...16 mm² rigid Plug-on neutral (upstream)
Wire stripping length	14 mm for top connection 13 mm for bottom connection
Tightening torque	3.5 N.m top 2 N.m bottom
Earth-leakage protection	Integrated

Environment

Standards	IEC 61009-2-2 IEC 61009-1 BS EN 61009-1
Product certifications	CB
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Overvoltage category	II
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-15...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	1.8 cm

Package 1 Length	13.1 cm
Package 1 Weight	193 g
Unit Type of Package 2	S02
Number of Units in Package 2	34
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.065 kg
Unit Type of Package 3	P12
Number of Units in Package 3	1088
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	246.08 kg

Logistical informations

Country of origin	TH
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	58
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	8fc881ba-477f-44ce-8482-1ca7af7406a4
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins