



Main

Range of product	Odace
Product or component type	Switch
Device presentation	Mechanism with fixing frame
Device application	Light control
Condition of use	Indoor

Complementary

Device mounting	Surface
Technology type	Electronic
Switch function	1-pole 1-way
Number of rocker	1
Actuator	Rocker
Fixing mode	By sticking
Colour tint	White (RAL 9003)
Surface finish	Glossy
Type of packing	Gift box
Load type	Low voltage
Service life in cycles	100000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Electrical durability	20000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Material	Thermoplastic ABS-UV stabilised: rocker PC (polycarbonate) GF10 FR: backplate
Height	71 mm
Width	71 mm
Depth	17 mm
Net weight	0.026 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-20...60 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	CE: WD21101201[RETURN]LCIE: CCA-FR_598285B
IK degree of protection	IK04

IP degree of protection	IP20
Environmental characteristic	Indoor use

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information